


**ASEL**




Program controller  
For RCA2/RCA

## List of models


Program controller for operating RCA2/RCA Series actuators. One unit can handle various controls.

Type	C	
Name	Program mode	Positioner Mode
External view		
Description	Both the actuator operation and communication with external equipment can be handled by a single controller. When two axes are connected, arc interpolation, path operations, and synchronization can be performed.	Up to 1500 positioning points are supported. Push-motion operation and teaching operation are also possible.
Position points	1500 points	
Number of control axes	Up to 2 axes	

## Model



# System configuration




## I/O Specifications


### Input section External input specifications

Item	Specifications
Input voltage	DC24V $\pm 10\%$
Input current	7mA / circuit
ON/OFF voltage	ON voltage (min.) NPN : DC16V / PNP : DC8V OFF voltage (max.) NPN : DC5V / PNP : DC19V
Isolation method	Photocoupler

#### NPN Specifications




#### PNP Specifications




### Output section External output specifications

Item	Specifications
Load Voltage	DC24V
Max. load current	100mA / 1 point 400mA / 8 points in total
Residual voltage (Max.)	Max 0.1mA / 1 point
Isolation method	Photocoupler

#### NPN Specifications



#### PNP Specifications



## Explanation of I/O Signal Functions

Two modes can be selected for the ASEL controller: "Program Mode," in which the actuator is operated by entering a program, and "Positioner Mode," in which PLC signals are received and the actuator is moved to designated positions. The Positioner Mode has the five input patterns listed below to enable various applications.

### Control Function by Type

Operation mode	Features
Program mode	Various operations including linear/arc interpolation operation, path operation ideal for coating processes, etc., arch-motion operation and palletizing operation can be performed using the Super SEL language that lets you program complex control actions using simple commands.
Positioner mode	Standard mode This is the basic mode from which operations can be conducted by designating position numbers and inputting the start signal. Push-motion operation and teaching operation are also possible.
	Product Change mode Multiple parts of the same shape with slightly different hole positions can be handled using movement commands to the same position numbers by simply changing the product type number.
	2-axis independent mode With a 2-axis controller, each axis can be commanded and operated separately.
	Teaching mode In this mode, the slider (rod) moves based on an external signal, when the actuator is stopped, the current location can be registered as position data.
	DS-S-C1 Compatible mode If you were using a DS-S-C1 controller, you can replace it with a ASEL controller without having to change the host programs. *This mode does not ensure actuator compatibility.

## Explanation of I/O Signal Functions

Slider  
Type

Mini

Standard

Controllers  
IntegratedRod  
Type

Mini

Standard

Controllers  
IntegratedTable/Arm  
/Flat Type

Mini

Standard

Gripper/  
Rotary TypeLinear Servo  
TypeCleanroom  
Type

Splash-Proof

Controllers

PMEC  
/AMECPSEP  
/ASEPROBO  
NET

ERC2

PCON

ACON

SCON

PSEL

ASEL

SSEL

XSEL

Pulse Motor

Servo Motor  
(24V)Servo Motor  
(200V)Linear  
Servo Motor


## Program mode

Pin Number	Category	Port No.	Program Mode	Functions
1A	P24		24V input	Connect 24V.
1B	Input	016	Select Program No. 1	Selects the program number to start. (Input as BCD values to ports 016 to 022)
2A		017	Select Program No. 2	
2B		018	Select Program No. 4	
3A		019	Select Program No. 8	
3B		020	Select Program No. 10	
4A		021	Select Program No. 20	
4B		022	Select Program No. 40	
5A		023	CPU reset	Resets the system to the same state as when the power is turned on.
5B		000	Start	Starts the program selected by ports 016 to 022.
6A		001	General-purpose input	Waits for external input via program instructions.
6B		002	General-purpose input	
7A		003	General-purpose input	
7B		004	General-purpose input	
8A		005	General-purpose input	
8B		006	General-purpose input	
9A		007	General-purpose input	
9B		008	General-purpose input	
10A		009	General-purpose input	
10B		010	General-purpose input	
11A		011	General-purpose input	
11B		012	General-purpose input	
12A		013	General-purpose input	
12B		014	General-purpose input	
13A		015	General-purpose input	
13B	Output	300	Alarm	Turns off when an alarm occurs. (Contact B)
14A		301	Ready	Turns on when the controller starts up normally and is in an operable state.
14B		302	General-purpose output	These outputs can be turned ON/OFF as desired via program instructions.
15A		303	General-purpose output	
15B		304	General-purpose output	
16A		305	General-purpose output	
16B		306	General-purpose output	
17A		307	General-purpose output	
17B	N		0V input	Connect 0V.

Note: This is for NPN. PNP will be different.

0V 24

Wiring Diagram




## Positioner mode

Pin Number	Category	Port No.	Positioner Standard Mode	Functions
1A	P24		24V input	Connect 24V.
1B	Input	016	Position input 10	Specifies the position numbers to move to, using port number 007 to 019. The number can be specified either as BCD or binary.
2A		017	Position input 11	
2B		018	Position input 12	
3A		019	Position input 13	
3B		020	-	
4A		021	-	
4B		022	-	
5A		023	Error reset	Resets minor errors. (Severe errors require a restart.)
5B		000	Start	Starts moving to the selected position.
6A		001	Home Return	Performs Home Return.
6B		002	Servo ON	Switches between Servo ON and OFF.
7A		003	Push	Performs a push motion.
7B		004	Pause	Pauses the motion when turned OFF, and resumes motion when turned ON.
8A		005	Cancel	Stops the motion when turned OFF. The remaining motion is canceled.
8B		006	Interpolation settings	When this signal turned ON for a 2-axis model, the actuator moves by linear interpolation.
9A		007	Position input 1	Specifies the position numbers to move to, using ports 007 to 019. The number can be specified either as BCD or binary.
9B		008	Position input 2	
10A		009	Position input 3	
10B		010	Position input 4	
11A		011	Position input 5	
11B		012	Position input 6	
12A		013	Position input 7	
12B		014	Position input 8	
13A		015	Position input 9	
13B	Output	300	Alarm	Turns off when an alarm occurs. (Contact B)
14A		301	Ready	Turns on when the controller starts up normally and is in an operable state.
14B		302	Positioning complete	Turns on when the movement to the destination is complete.
15A		303	Home Return complete	Turns on when the home return operation is complete.
15B		304	Servo ON output	Turns on when servo is ON.
16A		305	Pushing complete	Turns on when a push motion is complete.
16B		306	System battery error	Turns on when the system battery runs low (warning level).
17A		307	Absolute encoder battery error	Turns on when the battery for the absolute encoder runs low (warning level).
17B	N		0V input	Connect 0V.

Note: This is for NPN. PNP will be different.

0V 24

Wiring Diagram




## Explanation of I/O Signal Functions

## Positioner, Product-Type Change Mode

Pin Number	Category	Port No.	Positioner Product Type Change Mode	Functions
1A	P24		24V input	Connect 24V.
1B	Input	016	Position/Product Type Input 10	Specifies the position numbers to move to, and the product type numbers, using ports 007 to 022. The position and product type numbers are assigned by parameter settings. The number can be specified either as BCD or binary.
2A		017	Position/Product Type Input 11	
2B		018	Position/Product Type Input 12	
3A		019	Position/Product Type Input 13	
3B		020	Position/Product Type Input 14	
4A		021	Position/Product Type Input 15	
4B		022	Position/Product Type Input 16	
5A		023	Error reset	Resets minor errors. (Severe errors require a restart.)
5B		000	Start	Starts moving to the selected position.
6A		001	Home Return	Performs Home Return.
6B		002	Servo ON	Switches between Servo ON and OFF.
7A		003	Push	Performs a push motion.
7B		004	Pause	Pauses the motion when turned OFF, and resumes motion when turned ON.
8A		005	Cancel	Stops the motion when turned OFF. The remaining motion is canceled.
8B		006	Interpolation settings	When this signal is turned ON for a 2-axis model, the actuator moves by linear interpolation.
9A		007	Position/Product Type Input 1	Specifies the position numbers to move to, and the product type numbers, using ports 007 to 022. The position and product type numbers are assigned by parameter settings. The number can be specified either as BCD or binary.
9B		008	Position/Product Type Input 2	
10A		009	Position/Product Type Input 3	
10B		010	Position/Product Type Input 4	
11A		011	Position/Product Type Input 5	
11B		012	Position/Product Type Input 6	
12A	Output	013	Position/Product Type Input 7	Turns off when an alarm occurs (Contact B)
12B		014	Position/Product Type Input 8	
13A		015	Position/Product Type Input 9	
13B		300	Alarm	
14A		301	Ready	
14B		302	Positioning complete	
15A		303	Home Return complete	
15B		304	Servo ON output	
16A		305	Pushing complete	
16B		306	System battery error	
17A		307	Absolute encoder battery error	Turns on when the battery for the absolute encoder runs low (warning level).
17B	N		0V input	Connect 0V.

Note: This is for NPN. PNP will be different.

Wiring Diagram




## Positioner, 2-axis Independent Mode

Pin Number	Category	Port No.	Positioner 2-axis Independent Mode	Functions
1A	P24		24V input	Connect 24V.
1B	Input	016	Position input 7	Specifies the position numbers to move to, using ports 010 to 022. The position numbers on the 1st and 2nd axes are assigned by parameter settings. The number can be specified either as BCD or binary.
2A		017	Position input 8	
2B		018	Position input 9	
3A		019	Position input 10	
3B		020	Position input 11	
4A		021	Position input 12	
4B		022	Position input 13	
5A		023	Error reset	Resets minor errors. (Severe errors require a restart.)
5B		000	Start 1	Starts movement to the selected position number on the 1st axis.
6A		001	Home Return 1	Performs home return on the 1st axis.
6B		002	Servo ON 1	Switches between servo ON and OFF for the 1st axis.
7A		003	Pause 1	Pauses the motion on 1st axis when turned OFF, and resumes motion when turned ON.
7B		004	Cancel 1	Cancels the movement on the 1st axis.
8A		005	Start 2	Starts the movement to the selected position number on the 2nd axis.
8B		006	Home Return 2	Performs home return on the 2nd axis.
9A		007	Servo ON 2	Switches between servo ON and OFF for the 2nd axis.
9B		008	Pause 2	Pauses the motion on 2nd axis when turned OFF, and resumes when turned ON.
10A		009	Cancel 2	Cancels the movement on the 2nd axis.
10B	Output	010	Position input 1	Specifies the position numbers to move to, using ports 010 to 022. The position numbers on the 1st and 2nd axes are assigned by parameter settings. The number can be specified either as BCD or binary.
11A		011	Position input 2	
11B		012	Position input 3	
12A		013	Position input 4	
12B		014	Position input 5	
13A		015	Position input 6	
13B		300	Alarm	Turns off when an alarm occurs (Contact B)
14A		301	Ready	
14B		302	Positioning complete 1	
15A		303	Home Return complete 1	
15B		304	Servo ON output 1	
16A		305	Positioning complete 2	
16B		306	Home Return complete 2	
17A		307	Servo ON output 2	
17B	N		0V input	Connect 0V.

Note: This is for NPN. PNP will be different.

Wiring Diagram



## Explanation of I/O Signal Functions

Slider  
Type

Mini

Standard

Controllers  
IntegratedRod  
Type

Mini

Standard

Controllers  
IntegratedTable/Arm  
/Flat Type

Mini

Standard

Gripper/  
Rotary TypeLinear Servo  
TypeCleanroom  
Type

Splash-Proof

Controllers

PMEC  
/AMECPSEP  
/ASEPROBO  
NET

ERC2

PCON

ACON

SCON

PSEL

ASEL

SSEL

XSEL

Pulse Motor

Servo Motor  
(24V)Servo Motor  
(200V)Linear  
Servo Motor


## Positioner, Teaching Mode

Pin Number	Category	Port No.	Positioner Teaching Mode	Functions
1A	P24		24V input	Connect 24V.
1B	Input	016	JOG- on 1st axis	While the signal is on, the 1st axis is moved in the - (negative) direction.
2A		017	JOG+ on 2nd axis	While the signal is on, the 2nd axis is moved in the + (positive) direction.
2B		018	JOG- on 2nd axis	While the signal is on, the 2nd axis is moved in the - (negative) direction.
3A		019	Specify inching (0.01mm)	Specifies how much to move during inching. (Total of the values specified for ports 019 to 022)
3B		020	Specify inching (0.1mm)	
4A		021	Specify inching (0.5mm)	
4B		022	Specify inching (1mm)	
5A		023	Error reset	Resets minor errors. (Severe errors require a restart.)
5B		000	Start	Starts moving to selected position.
6A		001	Servo ON	Switches between Servo ON and OFF.
6B		002	Pause	Pauses the motion when turned OFF, and resumes motion when turned ON.
7A		003	Position input 1	Ports 003 to 013 are used to specify the position number to move, and the position number for inputting the current position. - When the teaching mode setting on port 014 is in the ON state, the current value is written to the specified position number.
7B		004	Position input 2	
8A		005	Position input 3	
8B		006	Position input 4	
9A		007	Position input 5	
9B		008	Position input 6	
10A		009	Position input 7	
10B		010	Position input 8	
11A		011	Position input 9	
11B		012	Position input 10	
12A		013	Position input 11	
12B	Output	014	Teaching mode setting	While the signal is input, the 1st axis is moved in the + (positive) direction.
13A		015	JOG+ on 1st axis	
13B		300	Alarm	Turns off when an alarm occurs. (Contact B)
14A		301	Ready	Turns on when the controller starts up normally and is in an operable state.
14B		302	Positioning complete	Turns on when the movement to the destination is complete.
15A		303	Home return complete	Turns on when the home return operation is complete.
15B		304	Servo ON output	Turns on when servo is ON.
16A		305	-	-
16B		306	System battery error	Turns on when the system battery runs low (warning level).
17A		307	Absolute encoder battery error	Turns on when the battery for the absolute encoder runs low (warning level).
17B	N		0V input	Connect 0V.

Note: This is for NPN. PNP will be different.

0V 24

Wiring Diagram




## Positioner, DS-S-C1 Compatible Mode

Pin Number	Category	Port No.	Positioner DS-S-C1 Compatible Mode	Functions
1A	P24		24V input	Connect 24V.
1B	Input	016	Position No. 1000	(Same as ports 004 through 015)
2A		017	-	-
2B		018	-	-
3A		019	-	-
3B		020	-	-
4A		021	-	-
4B		022	-	-
5A		023	CPU reset	Resets the system to the same state as when the power is turned on.
5B		000	Start	Starts moving to selected position.
6A		001	Hold (Pause)	Pauses the motion when turned ON, and resumes when turned OFF.
6B		002	Cancel	Stops the motion when turned ON. The remaining motion is canceled.
7A		003	Interpolation settings	When this signal is turned ON for a 2-axis model, the actuator moves by linear interpolation.
7B		004	Position No. 1	Ports 004 through 016 are used to specify the position number to move. The numbers are specified as BCD.
8A		005	Position No. 2	
8B		006	Position No. 4	
9A		007	Position No. 8	
9B		008	Position No. 10	
10A		009	Position No. 20	
10B		010	Position No. 40	
11A		011	Position No. 80	
11B		012	Position No. 100	
12A		013	Position No. 200	
12B		014	Position No. 400	
13A	Output	015	Position No. 800	Turns off when an alarm occurs. (Contact A)
13B		300	Alarm	
14A		301	Ready	Turns on when the controller starts up normally and is in an operable state.
14B		302	Positioning complete	Turns on when the movement to the destination is complete.
15A		303	-	-
15B		304	-	-
16A		305	-	-
16B		306	System battery error	Turns on when the system battery runs low (warning level).
17A		307	Absolute encoder battery error	Turns on when the battery for the absolute encoder runs low (warning level).
17B	N		0V input	Connect 0V.

Note: This is for NPN. PNP will be different.

0V 24

Wiring Diagram



## Table of specifications

	Item	Specifications
Basic Specifications	Connected actuator	RCA/RCA2 Series Actuator
	Input Voltage	DC24V $\pm 10\%$
	Power Supply Capacity	Control power supply (Max. 1.2A) + motor power supply (See the table below)
	Dielectric strength voltage	DC500V 10M $\Omega$ or higher
	Withstand voltage	AC500V 1 min.
	Rush current	Max. 30A
	Vibration resistance	XYZ directions 10 to 57Hz, One side amplitude: 0.035mm (continuous), 0.075mm (intermittent) 58 to 150 Hz 4.9 m/s <sup>2</sup> (continuous), 9.8 m/s <sup>2</sup> (intermittent)
Control specification	Number of control axes	1 axis / 2 axis
	Maximum total output of connected axis	60W (30W + 30W)
	Position detection method	Incremental encoder / Absolute encoder
	Speed setting	1mm/sec and up, the maximum depends on actuator specifications
	Acceleration setting	0.01G and up, the maximum depends on the actuator
	Operating method	Program operation / Positioner operation (switchable)
Program	Programming language	Super SEL language
	Number of programs	64 programs
	Number of program steps	2000 steps
	Number of multi-tasking programs	8 points
	Positioning Points	1500 points
	Data memory device	FLASHROM (A system-memory backup battery can be added as an option)
Communication	Data input method	Teaching pendant or PC software
	Number of I/O	24 input points / 8 output points (NPN or PNP selectable)
	I/O power	Externally supplied 24VDC $\pm 10\%$
	PIO cable	CB-DS-PIO $\square\square\square$ (supplied with the controller)
	Serial communications function	RS232C (D-Sub Half-pitch connector) / USB connector
	Field Network	DeviceNet, CC-Link, ProfiBus
	Motor Cable	CB-ACS-MA $\square\square\square$ (Max. 20m)
General specifications	Encoder cable	CB-ACS-PA $\square\square\square$ (Max. 20m)
	Protection function	Motor overcurrent, Motor driver temperature check, Overload check, Encoder open-circuit check Soft limit over, system error, battery error, etc.
	Ambient operating humidity and temperature	0 to 40°C 10 to 95% (non-condensing)
	Ambient atmosphere	Free from corrosive gases. In particular, there shall be no significant dust.
	Protection class	IP20
	Weight	Approx. 450g
	External dimensions	43 mm (W) x 159 mm (H) x 110 mm (D)

			1-Axis specification				2-Axis specification			
			Standard specifications/high acceleration and deceleration model		Power-saving		Standard specifications/high acceleration and deceleration model		Power-saving	
			Rated	Max. (Note2)	Rated	Max. (Note3)	Rated	Max. (Note2)	Rated	Max. (Note3)
Motor power supply capacity (Note1)	RCA RCA2	10W, 20W [Model symbol: 20]	1.3A	4.4A	1.3A	2.5A	2.6A	8.8A	2.6A	5.0A
		30W	1.3A	4.4A	1.3A	2.2A	2.6A	8.8A	2.6A	4.4A
		20W [Model symbol: 20S] SA4, RA3, TA5 type dedicated	1.7A	5.1A	1.7A	3.4A	3.4A	10.2A	3.4A	6.8A
	RCL	2W	0.8A	4.6A	—	—	1.6A	9.2A	—	—
		5W	1.0A	6.4A	—	—	2.0A	12.8A	—	—
		10W	1.3A	6.4A	—	—	2.6A	12.8A	—	—



(Note 1) For both 1-axis and 2-axis specifications, approx. 30.0A inrush current flows for 5 ms when the control power supply is turned on.

(Note 2) Max. current at accelerating/decelerating

(Note 3) Current reaches the maximum when detecting the servo motor excitation phase at the first servo on after the power is on. (Normal: Approx. 1 to 2 sec., Max.: 10 sec)



(Note 4) Other than motor power supply capacity, it increases 0.5A for control power.

## External Dimensions





## Name of Each Part



### 1 Motor connector for axis 1

Connect the motor cable of the axis 1 actuator.

### 2 Motor connector for axis 2

Connect the motor cable of the axis 2 actuator.

### 3 Brake switch for axis 1

This switch is used to release the axis brake. Setting it to the left position (RLS side) forcibly releases the brake, while setting it to the right position (NOM side) causes the controller to automatically control the brake.

### 4 Encoder connector for axis 1

Connect the encoder cable of the axis 1 actuator.

### 5 Brake switch for axis 2

This switch is used to release the axis brake.

Setting it to the left position (RLS side) forcibly releases the brake, while setting it to the right position (NOM side) causes the controller to automatically control the brake.

### 6 Encoder connector for axis 2

Connect the encoder cable of the axis 2 actuator.

### 7 Status indicator LEDs

These LEDs are used to indicate the operating condition of the controller.

The LED status indicators are as follows:

- PWR : Power is input to controller.
- RDY : The controller is ready to perform program operation.
- ALM : The controller is abnormal.
- EMG : An emergency stop is actuated and the drive source is cut off.
- SV1 : The axis 1 actuator servo is on.
- SV2 : The axis 2 actuator servo is on.

### 8 Panel unit connector

A connector for the panel unit (optional) that displays the controller status and error codes.

### 9 I/O Connector

A connector for interface I/Os.

34-pin flat cable connector for DIO (24IN/8OUT) interface.

I/O power is also supplied to the controller via this connector (Pin No. 1 and No. 34).

### 10 Mode switch

This switch is used to specify the running mode of the controller. The left position indicates the MANU (manual operation) mode, while the right position indicates the AUTO (automatic operation) mode. Teaching can only be performed in manual operation, and automatic operation using external I/Os is not possible in the MANU mode.

### 11 USB connector

A connector for PC connection via USB. If the USB connector is connected, the TP connector is disabled and all communication inputs to the TP connector are cut off.

### 12 Teaching pendant connector

A half-pitch I/O 26-pin connector that connects a teaching pendant when the running mode is MANU. A special conversion cable is needed to connect a conventional Dsub, 25-pin connector.

### 13 System-memory backup battery connector

If you wish to retain the various data recorded in the SRAM of the controller even after the power is cut off, connect the necessary battery to this connector. This battery is installed externally to the unit. The controller does not come standard with the battery (Option).

### 14 Motor power input connector

This connector is used to input the motor power. It consists of a 2-pin, 2-piece connector by Phoenix Contact.

### 15 External regenerative resistor connector

A connector for the regenerative resistor that must be connected when the built-in regenerative resistor alone does not offer sufficient capacity in high-acceleration/high-load operation, etc.

Whether or not an external regenerative resistor is necessary depends on the conditions of your specific application such as the axis configuration.

### 16 Control power/System input connector

This connector is used to connect the control power input, emergency stop switch, and enable switch. It consists of a Phoenix Contact 6-pin 2-piece connector.

### 17 Absolute-data backup battery connector for axis 1

A connector for the battery that backs up absolute data when the actuator uses an absolute encoder. Secure installation of the battery is the customer's responsibility.

### 18 Absolute-data backup battery connector for axis 2

A connector for the battery that backs up absolute data when the actuator uses an absolute encoder. Secure installation of the battery is the customer's responsibility.



## Option


### Teaching Pendant

- Features** This is a teaching device that provides information on functions such as position input, test runs, and monitoring.

**Model**


Model	Description
SEL-T-J	Standard type with adapter cable
SEL-TD-J	Equipped with a deadman switch and adapter cable

**Configuration**



**SEL-T dedicated options**

- Wall-mounting hook Model HK-1
- Strap Model STR-1



**Specifications**



Item	SEL-T-J	SEL-TD-J
3-position Enable Switch	No	Yes
ANSI/UL standards	Non-compliant	Compliant
CE mark	Compliant	
Display	20 char. x 4 lines	
Ambient Operating Temp./Humidity	0~40°C 10~90% RH (non-condensing)	
Protective structure	IP54	
Weight	Approx. 0.4kg (not incl. cable)	

### PC Software (Windows Only)

- Features** A startup support software for entering programs/positions, performing test runs, and monitoring. More functions have been added for debugging, and improvements have been made to shorten the start-up time.


- Model** IA-101-X-MW-J (with RS232C cable + adapter cable)

**Configuration**



- Model** IA-101-X-USB (with USB cable)


**Configuration**



**Note:**  
Only versions 7.0.0.0 and later can be used with the PSEL controller.

### Panel Unit

- Features** Display device that shows the error code from the controller or the currently running program number.
- Model** PU-1 (Cable length: 3m)



### Absolute Data Backup Battery

- Features** Battery for saving absolute data, when operating an actuator with an absolute encoder. Same as the battery used for system memory backup.
- Model** AB-5



### System Memory Backup Battery

- Features** This battery is required when you are using global flags in the program and you want to retain your data even after the power has been turned OFF.
- Model** AB-5-CS (with case)  
AB-5 (Standalone battery)



## Option

## Dummy Plug

- Features** When connecting the ASEL controller to a computer with a USB cable, this plug is inserted in the teaching port to shut off the enable circuit.  
(Supplied with the PC software IA-101-X-USB)

**■ Model** DP-3



## USB Cable

- Features** A cable for connecting the controller to the USB port to a computer. A controller with no USB port (e.g. XSEL) can be connected to the USB port of a computer by connecting an RS232C cable to the USB cable via a USB adapter.  
(See PC software IA-101-X-USBMW)

**■ Model** CB-SEL-USB030 (Cable length: 3m)



## Adapter Cable

- Features** An adapter cable to connect the D-sub 25-pin connector from the teaching pendant or a PC to the teaching connector (half-pitch) of the ASEL controller.

**■ Model** CB-SEL-SJ002 (Cable length: 0.2m)



## Spare Parts


When you need spare parts after purchasing the product, such as when replacing a cable, refer to the list of models below.

## Motor cable

**Model** CB-ACS-MA

\* The standard motor cable is a robot cable.

\* Enter the cable length (L) into   . Compatible to a maximum of 20 meters.  
Ex.: 080 = 8 m



DF1E-3S-2.5C			
Wire	Color	Signal	Pin No.
AWG22 (crimped)	White	V	1
	Black	W	3


SLP-03V			
Pin No.	Signal	Color	Wire
1	U	Red	AWG22 (crimped)
2	V	White	
3	W	Black	

## Encoder cable/Encoder robot cable

**Model** CB-ACS-PA    / CB-ACS-PA    -RB

\* The standard cable for the encoder cable is a normal cable.  
A robot cable can be specified as an option.

\* Enter the cable length (L) into   . Compatible to a maximum of 20 meters.  
Ex.: 080 = 8 m



CN2			
Cable color	Signal	Pin No.	
Robot Cable	Standard Cable	Robot Cable	
White/Purple	Blue	LS+	18
White/Gray	Orange	LS-	17
Yellow	Green	BK+	16
Blue	Brown	BK-	15
White/Blue	Gray	ENA	14
White/Yellow	Red	ENB	13
White/Black	Black	ENB	12
Orange	Pink	ENB	11
Green	Purple	ENB	10
Purple	White	ENB	9
Gray	Blue/Red	VPS	8
Red	Orange/White	SV	7
Black	Green/White	GND	5
-	-	-	4
-	-	-	3
-	-	-	2
Ground	Ground	F.G	1


CN1			
Pin No.	Signal	Cable color	
1	ENA	Gray	White/Blue
2	ENB	Red	White/Yellow
3	ENB	Black	White/Black
4	ENB	Yellow	White/Gray
5	-	-	-
6	-	-	-
7	LS+	Blue	White/Purple
8	-	-	-
9	FG	Ground	Ground
10	ENB	Pink	Orange
11	ENB	Purple	Green
12	-	White	Purple
13	VPS	Blue/Red	Gray
14	SV	Orange/White	Red
15	GND	Green/White	Black
16	LS-	Orange	White/Gray
17	BK-	Brown	Blue
18	BK+	Green	Yellow

Plug housing : XMP-18V (JST)  
Socket contact : BXA-001T-P0.6 (JST)  
Retainer : XMS-09V (JST)

## Motor-Encoder Integrated Cable for RCA2

**Model** CB-ACS-MPA

\* Enter the cable length (L) into   . Compatible to a maximum of 20 meters.  
Ex.: 080 = 8 m




Signal	Pin No.	(Wire color)	Pin No.	Signal
U	1	Red	A1	U
V	2	Yellow	B1	V
W	3	Black	A2	W
			B2	NC
			A3	NC
			B3	NC
BK+	16	Yellow (Red ●)	A4	BK+
BK-	15	Yellow (Blue ●)	B4	BK-
LS+	18	Pink (Red ●)	A5	LS+
LS-	17	Pink (Blue ●)	B5	LS-
A+	14	White (Red ●)	A6	A+
A-	13	White (Blue ●)	B6	A-
B+	12	Orange (Red ●)	A7	B+
B-	11	Orange (Blue ●)	B7	B-
Z+	10	Gray (Red ●)	A8	Z+
Z-	9	Gray (Blue ●)	B8	Z-
-	8	Orange (Red ● Contiguous)	A9	-
VCC	7	Orange (Blue ● Contiguous)	B9	VPS
GND	5	Gray (Red ● Contiguous)	A10	VCC
NC	1	Gray (Blue ● Contiguous)	B10	GND
			A11	NC
			B11	FG

Shield

## I/O Flat Cable

**Model** CB-DS-PIO

\* Enter the cable length (L) into   . Compatible to a maximum of 10 meters.  
Ex.: 080 = 8 m



Pin No.	Color	Wire	Pin No.	Color	Wire
1A	Brown 1		9B	Gray 2	
1B	Red 1		10A	White 2	
2A	Orange 1		10B	Black 2	
2B	Yellow 1		11A	Brown-3	
3A	Green 1		11B	Red 3	
3B	Blue 1		12A	Orange 3	
4A	Purple 1		12B	Yellow 3	
4B	Gray 1		13A	Green 3	
5A	White 1		13B	Blue 3	
5B	Black 1		14A	Purple 3	
6A	Brown-2		14B	Gray 3	
6B	Red 2		15A	White 3	
7A	Orange 2		15B	Black 3	
7B	Yellow 2		16A	Brown-4	
8A	Green 2		16B	Red 4	
8B	Blue 2		17A	Orange 4	
9A	Purple 2		17B	Yellow 4	