


# RCP5-RA4C ROBO Cylinder, Rod Type, Motor Unit Coupled, Actuator Width 40mm, 24V Pulse Motor

Model	RCP5	RA4C	WA	35P			P3		
Specification	Series	Type	Encoder type	Motor type	Lead	Stroke	Applicable controllers	Cable length	Options
Items			WA: Battery-less absolute specification	35P: Pulse motor, size 35□	16: 16mm 10: 10mm 5: 5mm 2.5: 2.5mm	60: 60mm 410: 410mm (Every 50mm)	P3: PCON-CA MSEP MSEL	N: No cable P: 1m S: 3m M: 5m X□: Specified length R□: Robot cable	Please refer to the options table below.

\*Controller is not included.

## Radial Load Applicable




\* Depending on the model, there may be some limitations to using the vertical mount position. Please refer to P.59 for details.



- POINT**  
Note on selection
- The actuator specification displays the payload's maximum value, but it will vary depending on the acceleration. Please refer to the "Selection Guidelines" (RCP5 Payload by Speed/Acceleration Table) on P. 61.
  - Please refer to P. 59 for push-motion operation.
  - The radial cylinder is equipped with a built-in guide. Please refer to the graphs shown in P. 65 and after for the allowable load mass.

## Correlation Diagrams of Speed and Payload



## Actuator Specifications

### Lead and Payload

Model number	Lead (mm)	Connected controller	Maximum payload		Maximum push force (N)	Stroke (mm)
			Horizontal (kg)	Vertical (kg)		
RCP5-RA4C-WA-35P-16-①-P3-②-③	16	High-output enabled	6	1.5	48	60~410 (Every 50mm)
		High-output disabled				
RCP5-RA4C-WA-35P-10-①-P3-②-③	10	High-output enabled	15	2.5	77	
		High-output disabled				
RCP5-RA4C-WA-35P-5-①-P3-②-③	5	High-output enabled	28	5	155	
		High-output disabled				
RCP5-RA4C-WA-35P-2.5-①-P3-②-③	2.5	High-output enabled	40	10	310	
		High-output disabled	36			

Legend: ① Stroke ② Cable length ③ Options \*Please refer to P. 59 for push-motion operation.

### Stroke and Maximum Speed

Lead (mm)	Connected controller	Maximum speed (Unit: mm/s)	
		60~360 (Every 50mm)	410 (mm)
16	High-output enabled	1,120	1,080
	High-output disabled	840	
10	High-output enabled	700	685
	High-output disabled		
5	High-output enabled	350	340
	High-output disabled		
2.5	High-output enabled	175	170
	High-output disabled		

### ① Stroke

Stroke (mm)	Standard price
60	-
110	-
160	-
210	-
260	-
310	-
360	-
410	-

### ③ Options

Name	Option code	Reference page	Standard price
Brake	B	→P. 11	-
Cable exit direction (Top)	CJT	→P. 11	-
Cable exit direction (Right)	CJR	→P. 11	-
Cable exit direction (Left)	CJL	→P. 11	-
Cable exit direction (Bottom)	CJB	→P. 11	-
Flange	FL	→P. 12	-
Tip adapter (Flange)	FFA	→P. 12	-
Tip adapter (Internal thread)	NFA	→P. 13	-
Tip adapter (Keyway)	KFA	→P. 13	-
Non-motor end specification	NM	→P. 11	-

### ② Cable Length

Type	Cable code	Standard price
Standard type	P (1m)	-
	S (3m)	-
	M (5m)	-
Special length	X06 (6m) ~X10 (10m)	-
	X11 (11m)~X15 (15m)	-
	X16 (16m)~X20 (20m)	-
	R01 (1m) ~R03 (3m)	-
Robot cable	R04 (4m) ~R05 (5m)	-
	R06 (6m) ~R10 (10m)	-
	R11 (11m)~R15 (15m)	-
	R16 (16m)~R20 (20m)	-

\*Please refer to P. 89 for maintenance cables.

## Actuator Specifications

Item	Description
Drive system	Ball screw Ø8mm, rolled C10
Positioning repeatability	±0.02mm
Lost motion	0.1mm or less
Rod	Ø20mm Aluminum
Rod non-rotation precision (*1)	0 deg.
Allowable load and torque on rod tip	Refer to table in the page on the right, refer to P. 65
Rod tip overhang distance	100mm or less
Ambient operating temperature, humidity	0 to 40°C, 85% RH or less (Non-condensing)


(\*1) Rod's angular displacement in rotational direction with no applied load is shown.

Dimensions

CAD drawings can be downloaded from our website. [www.intelligentactuator.com](http://www.intelligentactuator.com)




- \*1 When the rod is returning to its home position, please be careful of interference from surrounding objects, as it will travel until it reaches the ME.
  - \*2 The direction of width across flats varies depending on the product.
  - \*3 If the actuator is installed using the front housing and flange, make sure the actuator will not receive any external force.
- ME: Mechanical end  
SE: Stroke end




\*1 Two mounting holes on the rod side of the top of the base cannot be used.

■ Cable Exit Direction (Option)



■ Rod Deflection of RCP5-RA4C (Reference Values)



■ Dimensions and Mass by Stroke

L	Stroke		60	110	160	210	260	310	360	410
	Without brake	303	353	403	453	503	553	603	653	
With brake	334	384	434	484	534	584	634	684		
A	50	100	100	200	200	300	300	400		
B	35	85	85	185	185	285	285	385		
C	25	50	50	50	50	50	50	50		
D	0	0	1	1	2	2	3	3		
E	50	100	50	100	50	100	50	100		
F	8	8	10	10	12	12	14	14		
G	-	1	1	2	2	3	3	4		
H	50	50	100	50	100	50	100	50		
J	134	184	234	284	334	384	434	484		
K	179	229	279	329	379	429	479	529		
M	6	6	6	8	8	10	10	12		
Allowable static load on rod tip (N)	Without brake	55.8	44.6	37.1	31.7	27.6	24.3	21.7	19.5	
	Load offset 0mm	25.4	19.5	15.5	12.8	10.8	9.2	7.9	6.9	
Allowable dynamic load on rod tip (N)	Without brake	16.5	14.5	12.4	10.7	9.2	8.0	7.0	6.2	
	Load offset 100mm	16.5	14.5	12.4	10.7	9.2	8.0	7.0	6.2	
Allowable static torque on rod tip (N-m)	Without brake	5.6	4.5	3.8	3.2	2.8	2.5	2.3	2.1	
	With brake	1.7	1.5	1.2	1.1	0.9	0.8	0.7	0.6	
Mass (kg)	Without brake	1.1	1.2	1.3	1.4	1.6	1.7	1.8	1.9	
	With brake	1.3	1.4	1.5	1.6	1.8	1.9	2.0	2.1	

Applicable Controllers

The RCP5 series actuators can be operated by the controllers indicated below. Please select the type depending on your intended use.

Name	External view	Model number	Max. number of controlled axes	Maximum number of positioning points	Input power	Standard price	Reference page
Positioner type (High-output specification)		PCON-CA-35PWAI-①-2-0	1	512 points	DC24V	-	→P. 69
Pulse train type (High-output specification)		PCON-CA-35PWAI-PL⑤-2-0				-	
Network type (High-output specification)		PCON-CA-35PWAI-③-0-0				-	
Solenoid valve multi-axis type (PIO specification)		MSEP-④-①-①-①-①-2-0	4 (when high-output enabled) LC: 6 (3 when high-output enabled)	3 points		-	→P. 77
Solenoid valve multi-axis type (Network specification)		MSEP-④-①-①-①-①-0-0				256 points	
Program control multi-axis type		MSEL-PC-1-35PWAI-①-2-4	4	30,000 points	Single-phase AC 100V~230V	-	→P. 87
Program control multi-axis type (w/network board)		MSEL-PC-1-35PWAI-③-0-4					
Program control multi-axis type (Safety category compliant spec.)		MSEL-PG-1-35PWAI-①-2-4					
Program control multi-axis type (Safety category compliant spec. w/network board)		MSEL-PG-1-35PWAI-③-0-4					

\*Above MSEL models are for single-axis specification \*① I/O type (NP/PN) \*③ Number of axes  
 \*③ Field network specification code \*④ C or LC \*⑤ N (NPN specification) or P (PNP specification) code  
 \*The high output enabled operation is only available when the "High-output setting specs" is selected in the MSEP-C/LC.