


# RCP5-RA6R ROBO Cylinder, Rod Type, Side-mounted Motor Type, Actuator Width 58mm, 24V Pulse Motor


|                     |        |      |   |                            |  |                                     |                             |   |  |
|---------------------|--------|------|---|----------------------------|--|-------------------------------------|-----------------------------|---|--|
| Model               | RCP5   | RA6R | WA                                      | 42P                        |  |                                     | P3                          |   |  |
| Specification Items | Series | Type | Encoder type                            | Motor type                 | Lead                                     | Stroke                              | Applicable controllers      | Cable length  | Options                                  |
|                     |        |      | WA: Battery-less absolute specification | 42P: Pulse motor, size 42□ | 20: 20mm<br>12: 12mm<br>6: 6mm<br>3: 3mm | 65: 65mm<br>415: 415mm (Every 50mm) | P3: PCON-CA<br>MSEP<br>MSEL | N: No cable<br>P: 1m<br>S: 3m<br>M: 5m<br>X□: Specified length<br>R□: Robot cable | Please refer to the options table below. |

\*Controller is not included.

## Radial Load Applicable



\* Depending on the model, there may be some limitations to using the vertical mount position. Please refer to P.59 for details.




The figure above is the motor side-mounted to the left (ML).

**POINT**  
Note on selection

- The actuator specification displays the payload's maximum value, but it will vary depending on the acceleration. Please refer to the "Selection Guidelines" (RCP5 Payload by Speed/Acceleration Table) on P. 61.
- Please refer to P. 59 for push-motion operation.
- The radial cylinder is equipped with a built-in guide. Please refer to the graphs shown in P. 65 and after for the allowable load mass.

## Correlation Diagrams of Speed and Payload



## Actuator Specifications

### Lead and Payload

| Model number                 | Lead (mm) | Connected controller | Maximum payload |               | Maximum push force (N) | Stroke (mm)         |
|------------------------------|-----------|----------------------|-----------------|---------------|------------------------|---------------------|
|                              |           |                      | Horizontal (kg) | Vertical (kg) |                        |                     |
| RCP5-RA6R-WA-42P-20-①-P3-②-③ | 20        | High-output enabled  | 6               | 1.5           | 56                     | 65~415 (Every 50mm) |
|                              |           | High-output disabled |                 |               |                        |                     |
| RCP5-RA6R-WA-42P-12-①-P3-②-③ | 12        | High-output enabled  | 25              | 4             | 93                     |                     |
|                              |           | High-output disabled |                 |               |                        |                     |
| RCP5-RA6R-WA-42P-6-①-P3-②-③  | 6         | High-output enabled  | 40              | 10            | 185                    |                     |
|                              |           | High-output disabled |                 |               |                        |                     |
| RCP5-RA6R-WA-42P-3-①-P3-②-③  | 3         | High-output enabled  | 60              | 20            | 370                    |                     |
|                              |           | High-output disabled | 40              |               |                        |                     |

Legend: ① Stroke ② Cable length ③ Options \*Please refer to P. 59 for push-motion operation.

### Stroke and Maximum Speed

(Unit: mm/s)

| Lead (mm) | Connected controller | 65~365 (Every 50mm) |          | 415 (mm) |
|-----------|----------------------|---------------------|----------|----------|
|           |                      | 65~365 (Every 50mm) | 415 (mm) |          |
| 20        | High-output enabled  | 800                 |          |          |
|           | High-output disabled | 640                 |          |          |
| 12        | High-output enabled  | 700                 |          |          |
|           | High-output disabled | 500                 |          |          |
| 6         | High-output enabled  | 450                 |          |          |
|           | High-output disabled | 250                 |          |          |
| 3         | High-output enabled  | 225                 | 220      |          |
|           | High-output disabled | 125                 |          |          |

### ① Stroke

| Stroke (mm) | Standard price | Stroke (mm) | Standard price |
|-------------|----------------|-------------|----------------|
| 65          | -              | 265         | -              |
| 115         | -              | 315         | -              |
| 165         | -              | 365         | -              |
| 215         | -              | 415         | -              |

### ③ Options

| Name                                      | Option code | Reference page | Standard price |
|---|-------------|----------------|----------------|
| Brake                                     | B           | →P. 11         | -              |
| Cable exit direction (Top)                | CJT         | →P. 11         | -              |
| Cable exit direction (Outside)            | CJO         | →P. 11         | -              |
| Cable exit direction (Bottom)             | CJB         | →P. 11         | -              |
| Flange                                    | FL          | →P. 12         | -              |
| Tip adapter (Flange)                      | FFA         | →P. 12         | -              |
| Tip adapter (Internal thread)             | NFA         | →P. 13         | -              |
| Tip adapter (Keyway)                      | KFA         | →P. 13         | -              |
| Motor side-mounted to the left (Standard) | ML          | →P. 11         | -              |
| Motor side-mounted to the right           | MR          | →P. 11         | -              |
| Non-motor end specification               | NM          | →P. 11         | -              |

Depending on the stroke, some rod attachment options are not available. Also, when selecting the shorter strokes, please be careful of nearby objects. Some interference may occur. Please refer to P. 14.

### ② Cable Length

| Type           | Cable code          | Standard price |
|----------------|---------------------|----------------|
| Standard type  | P (1m)              | -              |
|                | S (3m)              | -              |
|                | M (5m)              | -              |
| Special length | X06 (6m) ~X10 (10m) | -              |
|                | X11 (11m)~X15 (15m) | -              |
|                | X16 (16m)~X20 (20m) | -              |
|                | R01 (1m) ~R03 (3m)  | -              |
| Robot cable    | R04 (4m) ~R05 (5m)  | -              |
|                | R06 (6m) ~R10 (10m) | -              |
|                | R11 (11m)~R15 (15m) | -              |
|                | R16 (16m)~R20 (20m) | -              |

\*Please refer to P. 89 for maintenance cables.

## Actuator Specifications

| Item                                    | Description   |
|---|---|
| Drive system                            | Ball screw Ø10mm, rolled C10                            |
| Positioning repeatability (*1)          | ±0.02mm [±0.03mm]                                       |
| Lost motion                             | 0.1mm or less   |
| Rod                                     | Ø25mm Aluminum  |
| Rod non-rotation precision (*2)         | 0 deg.  |
| Allowable load and torque on rod tip    | Refer to table in the page on the right, refer to P. 65 |
| Rod tip overhang distance               | 100mm or less   |
| Ambient operating temperature, humidity | 0 to 40°C, 85% RH or less (Non-condensing)              |

(\*1) The values in brackets [ ] are for Lead 20.

(\*2) Rod's angular displacement in rotational direction with no applied load is shown.


Dimensions

CAD drawings can be downloaded from our website. [www.intelligentactuator.com](http://www.intelligentactuator.com)




- \*1 When the rod is returning to its home position, please be careful of interference from surrounding objects, as it will travel until it reaches the ME.
- \*2 The direction of width across flats varies depending on the product.
- \*3 If the actuator is installed using the front housing and flange, make sure the actuator will not receive any external force.

ME: Mechanical end  
SE: Stroke end




■ Cable Exit Direction (Option)



\*The figure above is for the motor side-mounted to the left (ML).

■ Rod Deflection of RCP5-RA6R (Reference Values)



■ Dimensions and Mass by Stroke

| Stroke                                    | 65    | 115   | 165   | 215   | 265   | 315   | 365   | 415   |
|---|-------|-------|-------|-------|-------|-------|-------|-------|
| L   | 228   | 278   | 328   | 378   | 428   | 478   | 528   | 578   |
| A   | 0     | 100   | 100   | 200   | 200   | 300   | 300   | 400   |
| B   | 0     | 85    | 85    | 185   | 185   | 285   | 285   | 385   |
| C   | 1     | 1     | 2     | 2     | 3     | 3     | 4     | 4     |
| D   | 4     | 4     | 6     | 6     | 8     | 8     | 10    | 10    |
| E   | 0     | 0     | 0     | 1     | 1     | 2     | 2     | 3     |
| F   | 4     | 6     | 6     | 8     | 8     | 10    | 10    | 12    |
| G   | 0     | 1     | 1     | 1     | 1     | 1     | 1     | 1     |
| H   | 2     | 3     | 3     | 3     | 3     | 3     | 3     | 3     |
| J   | 172   | 222   | 272   | 322   | 372   | 422   | 472   | 522   |
| K   | 202.3 | 252.3 | 302.3 | 352.3 | 402.3 | 452.3 | 502.3 | 552.3 |
| Allowable static load on rod tip (N)      | 113.8 | 92.6  | 78.0  | 67.3  | 59.0  | 52.5  | 47.2  | 42.8  |
| Allowable dynamic load on rod tip (N)     | 45.7  | 36.3  | 29.8  | 25.1  | 21.6  | 18.8  | 16.6  | 14.7  |
| Load offset 0mm                           | 32.1  | 28.3  | 24.6  | 21.5  | 18.9  | 16.7  | 14.9  | 13.4  |
| Load offset 100mm                         | 32.1  | 28.3  | 24.6  | 21.5  | 18.9  | 16.7  | 14.9  | 13.4  |
| Allowable static torque on rod tip (N·m)  | 11.5  | 9.4   | 7.9   | 6.8   | 6.0   | 5.4   | 4.9   | 4.5   |
| Allowable dynamic torque on rod tip (N·m) | 3.2   | 2.8   | 2.5   | 2.1   | 1.9   | 1.7   | 1.5   | 1.3   |
| Mass (kg)                                 | 2.2   | 2.4   | 2.6   | 2.8   | 3.0   | 3.3   | 3.5   | 3.7   |
| Without brake                             | 2.2   | 2.4   | 2.6   | 2.8   | 3.0   | 3.3   | 3.5   | 3.7   |
| With brake                                | 2.4   | 2.6   | 2.8   | 3.0   | 3.2   | 3.5   | 3.7   | 3.9   |

Applicable Controllers

The RCP5 series actuators can be operated by the controllers indicated below. Please select the type depending on your intended use.

| Name  | External view | Model number           | Max. number of controlled axes                                       | Maximum number of positioning points | Input power               | Standard price | Reference page |
|---|---------------|------------------------|--|--------------------------------------|---------------------------|----------------|----------------|
| Positioner type (High-output specification)                                       |               | PCON-CA-42PWAI-①-2-0   | 1  | 512 points                           | DC24V                     | -              | →P.69          |
| Pulse train type (High-output specification)                                      |               | PCON-CA-42PWAI-PL②-2-0 |  |                                      |                           | -              |                |
| Network type (High-output specification)  |               | PCON-CA-42PWAI-③-0-0   |  |                                      |                           | -              |                |
| Solenoid valve multi-axis type (PIO specification)                                |               | MSEP-④-⑤-⑥-⑦-2-0       | 4 (4 when high-output enabled)<br>LC: 6 (3 when high-output enabled) | 3 points                             |                           | -              | →P.77          |
| Solenoid valve multi-axis type (Network specification)                            |               | MSEP-④-⑤-⑥-⑦-0-0       |  |                                      |                           | 256 points     |                |
| Program control multi-axis type   |               | MSEL-PC-1-42PWAI-①-2-4 | 4  | 30,000 points                        | Single-phase AC 100V~230V | -              | →P.87          |
| Program control multi-axis type (w/network board)                                 |               | MSEL-PC-1-42PWAI-②-0-4 |  |                                      |                           |                |                |
| Program control multi-axis type (Safety category compliant spec.)                 |               | MSEL-PG-1-42PWAI-①-2-4 |  |                                      |                           |                |                |
| Program control multi-axis type (Safety category compliant spec. w/network board) |               | MSEL-PG-1-42PWAI-②-0-4 |  |                                      |                           |                |                |

\*Above MSEL models are for single-axis specification  
 \*① I/O type (NP/PN)  
 \*② Field network specification code  
 \*③ C or LC  
 \*④ Number of axes  
 \*⑤ N (NPN specification) or P (PNP specification) code  
 \*The high output enabled operation is only available when the "High-output setting specs" is selected in the MSEP-C/LC.