

Slider Type

Mini

Standard

Controllers Integrated

Rod Type

Mini

Standard

Controllers Integrated

Table/ Arm/ Flat Type

Mini

Standard

Gripper/ Rotary Type

Linear Servo Type

Clean-room Type

Splash-Proof Type

Pulse Motor

Servo Motor (24V)

Servo Motor (200V)

Linear Servo Motor

RCS2-SA5C

ROBO Cylinder, Slider Type, Actuator Width 52mm, 200-V Servo Motor, Coupled

Model Specification Items	RCS2 — SA5C —	□	— 20 —	□	— □ —	□	— □ —	□	— □ —	□	— □ —	□
Series	— Type	— Encoder type	— Motor type	Lead	— Stroke	— Applicable controller	Cable length	— Options				
I: Incremental A: Absolute	20: Servo motor, 20W	20:20mm 12:12mm 6: 6mm 3: 3mm	50: 50mm 500: 500mm (50mm pitch increments)	T1: XSEL-J/K T2: SCON MSCON SSEL XSEL-P/Q XSEL-R/S	N: None P: 1m S: 3m M: 5m X□□: Custom length R□□: Robot cable	See Options below.						

* See page Pre-47 for details on the model descriptions.



*CE compliance is optional.

For High Acceleration/Deceleration

(excluding the 3-mm lead model)



*This product is equipped with a position adjusting screw at the A area shown above. (See dimensional drawing on the page to the right.)



- When the stroke increases, the maximum speed will drop to prevent the ball screw from reaching the critical rotational speed. Use the actuator specification table below to check the maximum speed at the stroke you desire.
- The load capacity is based on operation of standard model at 0.3G (0.2G for 3mm-lead), and operation of the high acceleration/deceleration model at 0.8G (excluding the 3mm-lead model). (Even when the acceleration/deceleration is dropped, the maximum load capacity values shown in the table below are the upper limits.)
- See page A-71 for details on push motion.

Technical References

Appendix P.5

Actuator Specifications

■ Leads and Payloads

Model number	Motor output (W)	Lead (mm)	Maximum payload (Horizontal kg)	Vertical (kg)	Rated thrust (N)	Stroke (mm)
RCS2-SA5C-①-20-20-②-③-④-⑤	20	20	2	0.5	10.7	50 to 500 (every 50mm)
RCS2-SA5C-①-20-12-②-③-④-⑤		12	4	1	16.7	
RCS2-SA5C-①-20-6-②-③-④-⑤		6	8	2	33.3	
RCS2-SA5C-①-20-3-②-③-④-⑤		3	12	4	65.7	

Code explanation ① Encoder type ② Stroke ③ Applicable Controller ④ Cable length ⑤ Options *See page A-71 for details on push motion. * The values enclosed in < > apply to vertical settings.

■ Stroke and Maximum Speed

(Unit: mm/s)

Stroke Lead	50~450 (every 50mm)	500 (mm)
20	1300 <800>	1300 <800>
12	800	760
6	400	380
3	200	190

①Encoder Type / ②Stroke

②Stroke (mm)	Standard price	
	①Encoder type	
	Incremental	Absolute
50	—	—
100	—	—
150	—	—
200	—	—
250	—	—
300	—	—
350	—	—
400	—	—
450	—	—
500	—	—

⑤Options

Name	Option code	Page	Standard Price
Brake	B	→ A-42	—
CE compliance	CE	→ A-42	—
Foot bracket	FT	→ A-47	—
For High Acceleration/Deceleration	HA	→ A-50	—
Home sensor	HS	→ A-50	—
Non-motor end specification	NM	→ A-52	—
Slider roller specification	SR	→ A-55	—

* The high-acceleration/deceleration option and the slider roller option cannot be used together.

* The high-acceleration/deceleration option cannot be used on the 3mm-lead model.

④ Cable Length

Type	Cable symbol	Standard price
Standard type	P (1m)	—
	S (3m)	—
	M (5m)	—
Special length	X06 (6m) ~ X10 (10m)	—
	X11 (11m) ~ X15 (15m)	—
	X16 (16m) ~ X20 (20m)	—
	R01 (1m) ~ R03 (3m)	—
Robot cable	R04 (4m) ~ R05 (5m)	—
	R06 (6m) ~ R10 (10m)	—
	R11 (11m) ~ R15 (15m)	—
	R16 (16m) ~ R20 (20m)	—


* See page A-59 for cables for maintenance.

Actuator Specifications

Item	Description
Drive method	Ball screw, ø10mm, rolled C10
Positioning repeatability	±0.02mm
Lost motion	0.1mm or less
Base	Material: Aluminum, white alumite treatment
Allowable static moment	Ma: 18.6 N·m, Mb: 26.6 N·m, Mc: 47.5 N·m
Allowable dynamic moment (*)	Ma: 4.9 N·m, Mb: 6.8 N·m, Mc: 11.7 N·m
Overhang load length	Ma direction: 150mm or less, Mb/Mc directions: 150mm or less
Ambient operating temperature/humidity	0 to 40°C, 85% RH max. (Non-condensing)

(*) When the traveling life is assumed as 5,000km.

Direction of allowable load moment.



Dimensional Drawings

CAD drawings can be downloaded from the website.

www.intelligentactuator.com



(*)1) Connect the motor and encoder cables here. See page A-59 for details on cables.

(*)2) After homing, the slider moves to the ME, therefore, please watch for any interference with surrounding objects.


ME : Mechanical end

SE : Stroke end

(*)3) Reference position for calculating the Ma moment

For Special Orders

Appendix P.15



Dimensions and Weights by Stroke

Stroke	50	100	150	200	250	300	350	400	450	500
L without brake	280.4	340.4	380.4	440.4	480.4	540.4	580.4	640.4	680.4	740.4
L with brake	319.4	369.4	419.4	469.4	519.4	569.4	619.4	679.4	719.4	769.4
M	142	192	242	292	342	392	442	492	542	592
N	50	100	100	200	200	300	300	400	400	500
P	35	85	85	185	185	285	285	385	385	485
R	42	42	92	42	92	42	92	42	92	42
U	—	1	1	2	2	3	3	4	4	5
m	4	4	4	6	6	8	8	10	10	12
Weight (kg)	1.3	1.4	1.5	1.6	1.7	1.8	1.9	2	2.1	2.2

* Brake-equipped models are heavier by 0.3kg.

③ Applicable Controllers

RCS2-series actuators can be operated with the following controllers. Select an appropriate controller type according to your application.

Name	External view	Model number	Features	Maximum number of positioning points	Input power	Power supply capacity	Standard price	Reference page
Positioner mode		SCON-CA-20①②-NP-2-③	Up to 512 positioning points are supported.	512 points	Single-phase 100VAC	106 VA max. *Power supply capacity will vary depending on the controller, so please refer to the instruction manual for details.	—	→ P643
Solenoid valve mode			Actuators can be operated through the same control used for solenoid valves.	7 points				
Field network type			Movement by numerical specification is supported.	768 points				
Pulse-train input control type			Dedicated pulse-train input type	(—)				
Positioner multi-axis, network type		MSCON-C-1-20①②-VI-0-③	Up to 6 axes can be operated. Movement by numerical specification is supported.	256 points	Single-phase 200VAC 3-phase 200VAC (XSEL-P/Q/R/S ONLY)	—	→ P655	→ P685
Program control type, 1 to 2 axes		SSEL-CS-1-20①②-NP-2-③	Program operation is supported. Up to 2 axes can be operated.	20,000 points				
Program control type, 1 to 8 axes		XSEL-④-1-20①②-N1-EEE-2-⑤	Program operation is supported. Up to 8 axes can be operated.	Varies depending on the number of axes connected				

* This is for the single-axis MSON, SSEL, and XSEL. * ① indicates the encoder type (I: Incremental / A: Absolute). * Enter the code "HA" in ② when the high-acceleration/deceleration option is specified.

* ③ indicates the power-supply voltage type (1: 100V / 2: Single-phase 200V).

* ④ indicates the power-supply voltage type (1: 100V / 2: Single-phase 200V / 3: Three-phase 200V).

* ⑤ indicates the XSEL type (J / K / P / Q / R / S).

* ⑥ indicates field network specification symbol.

Slider Type

Mini

Standard

Controllers Integrated

Rod Type

Mini

Standard

Controllers Integrated

Table/Arm/Flat Type

Mini

Standard

Gripper/Rotary Type

Linear Servo Type

Clean-room Type

Splash-Proof Type

Pulse Motor

Servo Motor (24V)

Servo Motor (200V)

Linear Servo Motor