


RCP3-TA5C

ROBO Cylinder, Table Type, Actuator Width 55mm, Pulse Motor, Coupled

Model Specification Items	RCP3 — TA5C — I — 35P — □ — □ — □ — □ — □
Series	— Encoder type — Motor type — Lead — Stroke — Applicable controller — Cable length — Options
	I: Incremental * The Simple absolute encoder is also considered type "I".
	35P: Pulse motor, 35□ size
	10: 10mm 5: 5mm 2.5: 2.5mm
	25: 25mm ? : 100: 100mm (25mm pitch increments)
	P1: PCON-PL/PO/SE PSEL P3: PCON-CA PMEC/PSEP MSEP
	N: None P: 1m S: 3m M: 5m X□□: Custom Length
	See Options below.

* See page Pre-47 for details on the model descriptions.





Technical References Appendix P.5



- (1) Since the RCP3 series use a pulse motor, the load capacity decreases at high speeds. Check in the Speed vs. Load Capacity graph to see if your desired speed and load capacity are supported.
- (2) Please note that the maximum speed is different when used horizontally versus vertically.
- (3) The load capacity is based on operation at an acceleration of 0.3G (0.2G for the 2.5mm-lead model, or when used vertically). This is the upper limit of the acceleration.
- (4) See page A-71 for details on push motion.

Speed vs. Load Capacity

Due to the characteristics of the pulse motor, the RCP3 series' load capacity decreases at high speeds. In the table below, check if your desired speed and load capacity are supported.



Actuator Specifications

Leads and Payloads

(Note 1) Please note that the maximum load capacity decreases as the speed increases.

Model number	Lead (mm)	Max. Load Capacity (Note 1)		Rated thrust (N)	Stroke (mm)
		Horizontal (kg)	Vertical (kg)		
RCP3-TA5C-I-35P-10-①-②-③-④	10	~2	~1	34	25~100 (every 25mm)
RCP3-TA5C-I-35P-5-①-②-③-④	5	~4	~1.5	68	
RCP3-TA5C-I-35P-2.5-①-②-③-④	2.5	~6	~3	136	

Stroke and Maximum Speed

(Unit: mm/s)

Stroke Lead	25~100 (every 25mm)	
	10	465<400>
5	250	
2.5	125	

Code explanation ① Stroke ② Applicable Controller ③ Cable length ④ Options *See page A-71 for details on push motion. *The values enclosed in < > apply to vertical settings.

① Stroke

① Stroke (mm)	Standard price
25	—
50	—
75	—
100	—

③ Cable Length

Type	Cable symbol	Standard price
Standard (Robot Cables)	P (1m)	—
	S (3m)	—
	M (5m)	—
Special length	X06 (6m) ~ X10 (10m)	—
	X11 (11m) ~ X15 (15m)	—
	X16 (16m) ~ X20 (20m)	—
		—

*The standard cable is the motor-encoder integrated robot cable.

* See page A-59 for cables for maintenance.

④ Options

Name	Option code	See page	Standard price
Brake	B	→ A-42	—
Cable exit direction (top)	CJT	→ A-42	—
Cable exit direction (right)	CJR	→ A-42	—
Cable exit direction (left)	CJL	→ A-42	—
Cable exit direction (bottom)	CJB	→ A-42	—
Non-motor end specification	NM	→ A-52	—

Actuator Specifications

Item	Description
Drive System	Ball screw, ø8mm, rolled C10
Positioning Repeatability	±0.02mm
Lost Motion	0.1mm or less
Base	Material: Aluminum, special alumite treated
Allowable static moment	Ma: 25.5 N·m, Mb: 36.5 N·m, Mc: 56.1 N·m
Allowable dynamic moment (*)	Ma: 6.57 N·m, Mb: 9.32 N·m, Mc: 14.32 N·m
Overhang load length	Within the load moment range
Ambient operating temperature, humidity	0 to 40°C, 85% RH or less (Non-condensing)

(*) Based on 5,000km of traveling life

Directions of allowable load moments

