* See page Pre-47 for details on the model descriptions.

RCS2-TCA5N

Robo Cylinder, Mini Table Type, Short-Length Compact type, Actuator Width 48mm, 200V Servo Motor, Ball Screw Specification

Model Specification Items

RCS2 - TCA5N - IType — Encoder type — Motor type —

60

60:60W Servo

I: Incremental

specification

Lead

10: 10mm

2.5 : 2.5mm

5mm

Stroke

T2 Applicable controller 50: 50mm

T2: SCON-CA SSEL

XSEL-P/Q

N: None N: None
P: 1m
S: 3m
M:5m
X: Custom length
R: Robot cable

Cable length — Options

See options below.

RoHS *CE compliance is optional.



Technical References

(Unit: mm/s)

(1) The payload is the value when the actuator is operated at an acceleration of $0.3\,\mbox{G}$ (0.2G for 2.5mm-lead) horizontally and 0.2G vertically. The acceleration

(2) If the actuator is used vertically, pay attention to rod contact because the rod will come down when the power is turned off.

(3) See page A-71 for details on push motion.

Actuator Specifications

■ Leads and Payloads

Model number	Motor output (W)		, ,	Max. Load Capacity Horizontal (kg) Vertical (kg)		Rated thrust (N)	Positioning repeatability (mm)	Stroke (mm)		
RCS2-TCA5N-I-60-10-①-T2-②-③	60		10	5	1.5	89				
RCS2-TCA5N-I-60-5-①-T2-②-③		60	60	60 Ball screw	5	10	3	178	±0.02	50 75
RCS2-TCA5N-I-60-2.5-①-T2-②-③			2.5	20	6	356				

■ Stroke and Maximum Speed

Stroke Lead	50 (mm)	75 (mm)					
10	280<230>	380<330>					
5	250<230>	250					
2.5	125						

*The values enclosed in < > apply to vertical settings.

① Stroke

Stroke (mm)	Standard price
50	_
75	_

② Cable Length

selection

Туре	Cable symbol	Standard Price
	P (1m)	_
Standard	S (3m)	_
	M (5m)	_
Special length	X06 (6m) ~ X10 (10m)	_
	X11 (11m) ~ X15 (15m)	_
	X16 (16m) ~ X20 (20m)	_
Robot Cable	R01 (1m) ~ R03 (3m)	_
	R04 (4m) ~ R05 (5m)	_
	R06 (6m) ~ R10 (10m)	_
	R11 (11m) ~ R15 (15m)	_
	R16 (16m) ~ R20 (20m)	_

^{*} See page A-59 for cables for maintenance.

③ Options

Name	Option code	See page	Standard price
Brake	В	→ A-42	_
CE compliance	CE	→ A-42	_
Connector cable exits from the left	K1	→ A-51	_
Connector cable exits from the front	K2	→ A-51	_
Connector cable exits from the right	К3	→ A-51	_

Actuator Specifications

ltem	Description
Drive System	Ball screw, ø8mm, rolled C10
Lost Motion	0.1mm or less
Base	Material: Aluminum, white alumite treated
Allowable dynamic moment (*)	Ma: 15 N·m, Mb: 15 N·m, Mc: 7.1 N·m
Allowable static moment	Ma: 38.6 N·m, Mb: 38.6 N·m, Mc: 17.9 N·m
Overhang load length	Ma direction: 100mm or less, Mb, Mc direction: 100mm or less
Ambient operating temperature, humidity	0 to 40°C, 85% RH or less (Non-condensing)
Service life	5,000km or 50 million cycles

^(*) Based on 5,000km of traveling life

7<u>1 (Body)</u>

45.6 (Brake)

For Special Orders

(With Brake size)

2-M4 Depth 4

Secure at least 100mm

Appenai P.15


Flat Type




CAD drawings can be downloaded www.intelligentactuator.com


2D CAD


(*1) Connect the motor-encoder integrated cable here.
(*2) After homing, the slider moves to the ME, therefore, please watch for any interference with surrounding objects.






Model number: K1 Model number: K2 Model number: K3





L1

0



*Brake-equipped models are heavier by 0.26kg.

46

2-M5 Depth 10

(6.5)

■ Dimensions and Weight by Stroke

Dilliensions and Weight by Stroke							
Stroke	50	75					
L	130	155					
L1	126	151					
L2	108	133					
M	89	105.5					
Weight (kg)	1.3	1.5					

Applicable Controllers

* View from (A) in the figure above

RCS2 series actuators can be operated with the controllers indicated below. Select the type according to your intended application.

Name	External view	Model number	Features	Maximum number of positioning points	Input power	Power-supply capacity	Standard price	Reference page	
Positioner Type				Up to 512 positioning points are supported	512 points				
Solenoid mode	11	SCON SA COLAID A O	Can be operated with the same controls used for solenoid valves	7 points	Single- phase 100 VAC	218 VA max.	_	. DC42	
Network mode			SCON-CA-60I-NP-2-①	Can be moved by direct numerical specification	768 points	Single- phase	*Varies depending on the		→ P643
Pulse-train input control mode			Can be controlled using pulse trains	(—)	200 VAC	controller. Refer to the operation	_		
Program control type 1 or 2 axes		SSEL-CS-1-60I-NP-2-①	Program operation is supported Up to two axes can be operated	20,000 points	3-phase 200 VAC (XSEL-P/ Q only)	manual for details.	_	→ P685	
Program control type 1 or 6 axes	Pilled.	XSEL-(II)-1-60I-N1-EEE-2-3	Program operation is supported Up to six axes can be operated	20,000 points			_	→ P695	

*The values of SSEL and XSEL assume a 1-axis specification. *① indicates the type of power-supply voltage (1: 100 V/2: Single-phase 200 V). *⑩ indicates the XSEL type (P/Q).

Please note that this model cannot be connected to the XSEL-P/Q type (5-axis/6-axis), XSEL-R/S type, or MSCON.