P2-RTC/RTC

Model Specification Items

RCP2 —

* See page Pre-47 for details on the model descriptions.

Type — Encoder type — Motor type — Deceleration Ratio — Oscillation Angle -RTC: 330-deg |: Incremental The Simple absolute rotation encoder is also RTCI · Multiple

rotation

28P: Pulse motor, 20: 1/20 28□ size considered type "I".

28P -

References

deceleration ratio 30: 1/30 deceleration ratio

330: 330-degrees (RTC only) 360: 360-degrees (RTCL only)

P1: PCON-PL/PO/SE **PSEL** P3: PCON-CA


PMEC/PSEP MSEP


- Applicable controller — Cable length — Options N: None P: 1m S: 3m

NM: Non-motor end SA: Shaft adapter TA: Table adapter M:5m X□□: Custom length R□□: Robot cable

■ Speed vs. Load Capacity

Due to the characteristics of the pulse motor, the RCP2 series' load capacity decreases at high speeds. In the table below, check if your desired speed and load capacity are supported.





C E RoHS Technical

(1) The output torque decreases as the rotational speed increases. Check the Output Torque graph on the right to see whether the speed required for your desired motion is supported. (2) The allowable moment of inertia of the rotated work piece varies with the rotational speed. Check the Allowable Moment of Inertia graph on the right to see if the moment of inertia required for your desired motion is within the allowable range.

- (3) The rated acceleration while moving is 0.3G.
- (4) Please note that the PMEC/PSEP controllers cannot be used when performing infinite rotation with the multiple

Actuator Specifications

■ Leads and Payload

Model number	Deceleration Ratio	Max. Torque (N·m)	Allowable Movement of Inertia (kg · m²)	Oscillation Angle (deg)
RCP2-RTC-I-28P-20-330-①-②-③	1/20	1.1	0.01	330
RCP2-RTC-I-28P-30-330-①-②-③	1/30	1.7	0.015	330
RCP2-RTCL-I-28P-20-360-①-②-③	1/20	1.1	0.01	360
RCP2-RTCL-I-28P-30-360-①-②-③	1/30	1.7	0.015	300

■ Deceleration Ratio and Max. Speed

Stroke Deceleration ratio	330/360 (deg)
1/20	600
1/30	400
	(Unit: degrees/s)

Notes or selection

Туре	Oscillation Angle (deg)	Standard price
RTC	330	_
RTCL	360	_

②Cable Length

Туре	Cable symbol	Standard Price
	P (1m)	_
Standard	S (3m)	_
	M (5m)	_
	X06 (6m) ~ X10 (10m)	_
Special length	X11 (11m) ~ X15 (15m)	_
	X16 (16m) ~ X20 (20m)	_
	R01 (1m) ~ R03 (3m)	_
Robot Cable	R04 (4m) ~ R05 (5m)	_
	R06 (6m) ~ R10 (10m)	_
	R11 (11m) ~ R15 (15m)	_
	R16 (16m) ~ R20 (20m)	_

^{*} See page A-59 for cables for maintenance.

③ Options

News	0-4:	C	Chandand miles
Name	Option code	See page	Standard price
Reversed-rotation	NM	→ A-52	_
Shaft adapter	SA	→ A-54	_
Table adapter	TA	→ A-56	_

Actuator Specifications

Item	Description
Drive System	Hypoid gear
Positioning repeatability	±0.01 degrees
Homing accuracy	±0.01 degrees (RTC) / ±0.05 (RTCL)
Lost motion	±0.1 degrees
Allowable thrust load	50N
Allowable load moment	3.9 N·m
Weight	0.92kg
Ambient operating temperature, humidity	0 to 40°C, 85% RH or less (Non-condensing)

Dimensional Drawings


3D CAD

CAD drawings can be downloaded www.intelligentactuator.com


For Special Orders







(*1) Connect the motor and encoder cables here. See page A-59 for details on cables.



ø24h7 ø11H7 depth 10 4 +0.05 depth 2.5 4-M4 depth 8 ø4 ^{+0.03} depth 2.5 hollow hole ø10 through-hole ø15.4 depth 5.5

The position shown in the top view of the drawing is the home position for both the standard type and reversed rotation type (Option "-NM"). Looking from above, the standard type will rotate counter clockwise during homing, and it then moves clockwise afterward. The reverse rotation type will move clockwise during homing and then moves counter clockwise afterward. Please be aware that the homing direction cannot be changed after shipment. Please refer to the Appendix for the details.

*The bend radius R of the cable is the same as other models.

Weight (kg) 0.92

(1) A to	اطحملاه	o Con	trollers	
UAD	piicabi	ie con	troners	9

Name	External view	Model number	Features	Maximum number of positioning points	Input power	Power-supply capacity	Standard price	Reference page
Calanai d Valua Tura	***	PMEC-C-28PI-①-2-⑪	Easy-to-use controller, even for beginners		AC100V AC200V	Refer to P541	_	→ P537
Solenoid Valve Type		PSEP-C-28PI-①-2-0	Simple controller operable with the same signal as a solenoid valve	3 points		Refer to P555	_	→ P54
Solenoid valve multi-axis type PIO specification	dine.	MSEP-C	Positioner type based on PIO control, allowing up to 8 axes to be connected			Refer to P572	_	→ P563
Solenoid valve multi-axis type Network specification	iiii	MSEP-C	Field network-ready positioner type, allowing up to 8 axes to be connected	256 points				
Positioner type High-output specification		PCON-CA-28PI-①-2-0	Equipped with a high-output driver Positioner type based on PIO control	512 points			_	
Pulse-train type High-output specification		PCON-CA-28PI-PL□-2-0	Equipped with a high-output driver Pulse-train input type	(—)	DC24V	Refer to P618	_	→ P60
Field network type High-output specification		PCON-CA-28PI-ℚ-0-0	Equipped with a high-output driver Supporting 7 major field networks	768 points	DC24V		_	
Pulse Train Input Type (Differential Line Driver)		PCON-PL-28PI-①-2-0	Pulse train input type with differential line driver support	(—)		Refer to P628	_	
Pulse Train Input Type (Open Collector)		PCON-PO-28PI-①-2-0	Pulse train input type with open collector support				_	→ P623
Serial Communication Type	Ī	PCON-SE-28PI-N-0-0	Dedicated Serial Communication	64 points			_	
Program Control Type		PSEL-CS-1-28PI-①-2-0	Programmed operation is possible. Can operate up to 2 axes	1,500 points		Refer to P671	_	→ P66

Note:

RCP2-RTC/RTCL 404