

EC-RR7□AH



High Rigidity

Coupled Motor

Body width 75 mm

24v Stepper motor

Model Specification Items



Radial load specification
Radial Cylinder*



- (1) The actuator specifications display the payload's maximum value, but it will vary depending on the acceleration and speed. Please refer to "Table of Payload by Speed/Acceleration" for more details.
- (2) The Radial Cylinder is equipped with a guide. Please refer to P111 for details of the radial loads applied to the rod.
- (3) The value of the horizontal payload assumes the use of an external guide.
- (4) When performing a push-motion operation, please refer to the "Correlation between push force and current limit value." Push force is only a guide.
- (5) Depending on the ambient operating temperature, duty control is necessary. Please refer to P115 for cautions.
- (6) Special attention needs to be paid to the mounting orientation. Please refer to P33 for details.

Stroke

Stroke (mm)	EC-RR7□AH	Stroke (mm)	EC-RR7□AH
50	○	300	○
100	○	350	○
150	○	400	○
200	○	450	○
250	○	500	○

Cable Length

Cable code	Cable length
0	No cable (with connector)
1 ~ 3	1 ~ 3m
4 ~ 5	4 ~ 5m
6 ~ 10	6 ~ 10m

(Note) Robot cables.

Options

Name	Option code	Reference page
Brake	B	See P.101
Tip adapter (flange)	FFA	See P.101
Flange (front)	FL	See P.102
Tip adapter (female screw)	NFA	See P.103
Knuckle joint (Note 1)	NJ	See P.106
Knuckle joint + oscillation receiving bracket (Note 1)	NJPB	See P.107
Non-motor end specification	NM	See P.108
PNP specification	PN	See P.108
Clevis bracket (Note 1)	QR	See P.108
Clevis bracket + oscillation receiving bracket (Note 1)	QRPB	See P.109
Split motor and controller power supply specification	TMD2	See P.109
Battery-less absolute encoder	WA	See P.109
Wireless communication specification	WL	See P.109
Wireless axis-operation specification	WL2	See P.109

(Note) Please purchase a clevis bracket (QR or QRPB) and a knuckle joint (NJ or NJPB) together as a set. Mounting is to be done by customer.

Main specifications

Item		Description				
Lead	Ball screw lead (mm)	24	16	8	4	
Horizontal	Payload	Max. payload (kg) (energy-saving disabled)	20	50	60	80
		Max. payload (kg) (energy-saving enabled)	18	40	50	55
	Speed/acceleration/deceleration	Max. speed (mm/s)	860	700	350	175
		Min. speed (mm/s)	30	20	10	5
		Rated acceleration/deceleration (G)	0.3	0.3	0.3	0.3
Vertical	Payload	Max. payload (kg) (energy-saving disabled)	3	8	18	28
		Max. payload (kg) (energy-saving enabled)	3	5	17.5	26
	Speed/acceleration/deceleration	Max. speed (mm/s)	640	560	350	175
		Min. speed (mm/s)	30	20	10	5
		Rated acceleration/deceleration (G)	0.3	0.3	0.3	0.3
Push force	Pushing max. thrust force (N)*	182	273	547	1094	
	Pushing max. speed (mm/s)	20	20	20	20	
Brake	Brake holding specification	Non-excitation actuating solenoid brake				
	Brake holding force (kgf)	3	8	18	28	
Stroke	Min. stroke (mm)	50	50	50	50	
	Max. stroke (mm)	500	500	500	500	
	Stroke pitch (mm)	50	50	50	50	

Item	Description
Driving system	Ball screw φ12mm, Rolling C10
Positioning repeatability	±0.05mm
Lost motion	-
Linear guide	Linear motion infinite circulating type
Rod	φ30mm Material: Aluminum Hard alumite treatment
Rod non-rotation accuracy (Note 2)	0 degree
Ambient operation temperature/humidity	0~40°C, 85%RH or less (Non-condensing)
Degree of protection	IP20
Vibration & shock resistance	4.9m/s ² 100Hz or less
Overseas standards	CE marking, RoHS (Restriction of Hazardous Substances)
Motor type	Stepper motor
Encoder type	Incremental / battery-less absolute
Number of encoder pulses	800 pulse/rev

(Note 2) The rod tip displacement angle when no load is applied.

* Speed limitation applies to push motion. See the manual or contact IAI.

Table of Payload by Speed/Acceleration

Setting for energy-saving disabled Unit for payload is kg. Operations on the blank locations are not possible.

Lead 24

Orientation	Speed (mm/s)	Horizontal					Vertical				
		Acceleration (G)					Acceleration (G)				
		0.3	0.5	0.7	1	0.3	0.5				
	0	20	18	15	12	3	3				
	200	20	18	15	12	3	3				
	400	20	14	12	8	3	3				
	420	17	12	10	6	3	3				
	600	14	6	5	4	3	2				
	640	5	3	2	1.5	2	1				
	800	5	1	1							
	860	2	0.5								

Lead 16

Orientation	Speed (mm/s)	Horizontal					Vertical				
		Acceleration (G)					Acceleration (G)				
		0.3	0.5	0.7	1	0.3	0.5				
	0	50	40	35	30	8	8				
	140	50	40	35	30	8	8				
	280	50	35	25	20	7	7				
	420	25	18	14	10	4.5	4				
	560	10	5	3	2	2	1				
	700	2									

Lead 8

Orientation	Speed (mm/s)	Horizontal					Vertical				
		Acceleration (G)					Acceleration (G)				
		0.3	0.5	0.7	1	0.3	0.5				
	0	60	50	45	40	18	18				
	70	60	50	45	40	18	18				
	140	60	50	45	40	16	12				
	210	60	40	31	26	10	9				
	280	34	20	15	11	5	4				
	350	12	4	1		2	1				

Lead 4

Orientation	Speed (mm/s)	Horizontal					Vertical				
		Acceleration (G)					Acceleration (G)				
		0.3	0.5	0.7	1	0.3	0.5				
	0	80	70	65	60	28	28				
	35	80	70	65	60	28	28				
	70	80	70	65	60	28	28				
	105	80	60	50	40	18	18				
	140	50	30	20	15	12	10				
	175	15				2					

■ **Setting for energy-saving enabled** Unit for payload is kg. Operations on the blank locations are not possible

Lead 24

Orientation	Horizontal			Vertical
	Acceleration (G)			
Speed (mm/s)	0.3	0.7	0.3	
0	18	9.5	3	
200	18	9.5	3	
420	10	5	1.5	
630	1			

Lead 16

Orientation	Horizontal			Vertical
	Acceleration (G)			
Speed (mm/s)	0.3	0.7	0.3	
0	40	25	5	
140	40	25	5	
280	18	12	2	
420	1.5	1		

Lead 8

Orientation	Horizontal			Vertical
	Acceleration (G)			
Speed (mm/s)	0.3	0.7	0.3	
0	50	30	17.5	
70	50	30	17.5	
140	50	30	7	
210	14	7	2	

Lead 4


Orientation	Horizontal			Vertical
	Acceleration (G)			
Speed (mm/s)	0.3	0.7	0.3	
0	55	50	26	
35	55	50	26	
70	55	50	13	
105	30	15	2	

Stroke and maximum speed


Lead (mm)	Energy-saving mode	50-500 (per 50mm)
24	Disabled	860<640>
	Enabled	630<420>
16	Disabled	700<560>
	Enabled	420<280>
8	Disabled	350
	Enabled	210
4	Disabled	175
	Enabled	105

(Note) Figures in <> represent vertical operations. (Unit is mm/s)

Correlation between push force and current limit value




Rod deflection (reference value)



Dimensions

*1 When the rod is returning to its home position, please be careful of interference from surrounding objects, as it will travel until it reaches the M.E.
*2 The direction of width across flats varies depending on the product. Those flats cannot be used for reference plane.

CAD drawings can be downloaded from our website.
www.intelligentactuator.com



■ **Dimensions by stroke**

Stroke	50	100	150	200	250	300	350	400	450	500	
L	Without brake	417.5	467.5	517.5	567.5	617.5	667.5	717.5	767.5	817.5	867.5
	With brake	467.5	517.5	567.5	617.5	667.5	717.5	767.5	817.5	867.5	917.5
A	260.5	310.5	360.5	410.5	460.5	510.5	560.5	610.5	660.5	710.5	
B	208.5	258.5	308.5	358.5	408.5	458.5	508.5	558.5	608.5	658.5	
C	50	0	50	0	50	0	50	0	50	0	
D	1	2	2	3	3	4	4	5	5	6	
E	6	6	8	8	10	10	12	12	14	14	
J	150	200	250	300	350	400	450	500	550	600	

■ **Mass by stroke**

Stroke	50	100	150	200	250	300	350	400	450	500	
Mass (kg)	Without brake	4	4.4	4.7	5	5.4	5.7	6	6.4	6.7	7
	With brake	4.5	4.9	5.2	5.5	5.9	6.2	6.5	6.9	7.2	7.5

Applicable controller

(Note) The EC series is equipped with a controller built-in. Please refer to P116 for details.