

# RCP3-RA2BR

ROBO Cylinder, Mini Rod Type, Side-mounted Motor Type, Actuator Width 28mm  
Pulse Motor, Ball Screw Specification/Lead Screw Specification

Model Specification Items	<b>RCP3</b> — <b>RA2BR</b> — <b>I</b> — □ — □ — □ — □ — □ — □
Series	Type — Encoder type — Motor type — Lead — Stroke — Applicable controller — Cable length — Options
	I: Incremental *The Simple absolute encoder is also considered type "I". 20P: Pulse motor, size 20□ Standard type 20SP: Pulse motor, size 20□ High thrust type 6: Ball screw 6mm 4: Ball screw 4mm 2: Ball screw 2mm 1: Ball screw 1mm 6S: Lead screw 6mm 4S: Lead screw 4mm 2S: Lead screw 2mm 25: 25mm } 150: 150mm (every 25mm) P1: PCON-PL/PO/SE PSEL P3: PCON-CA PMEC/PSEP MSEP N: None P: 1m S: 3m M: 5m X□□: Custom length See Options below. * Be sure to specify either "ML" or "MR" as the motor side-mounted direction.

\* See page Pre-47 for details on the model descriptions.




The "Motor side-mounted to the left (ML)" option is selected for the actuator shown above.

Technical References Appendix P.5

- POINT** Notes on Selection
- The payload is the value when the actuator is operated at an acceleration of 0.3G (0.2G for the lead screw specification, if used vertically). The acceleration limit is the value indicated above.
  - The horizontal payload is the value when used in combination with an external guide. Please note that if an external force is applied to the rod in a direction other than the proper direction the rod travels, the detent may get damaged.
  - The maximum pushing force is the value when the actuator is operated at a speed of 5mm/s. See page A-71 for details on push motion.
  - Service life decreases significantly if used in a dusty environment.

### Correlation Diagrams of Speed and Load Capacity

With the RCP3 series, due to the characteristics of the pulse motor, load capacity decreases as the speed increases. Use the chart below to confirm that the desired speed and load capacity requirements are met.



### Actuator Specifications

#### Leads and Payloads

Model number	Motor type	Feed screw	Lead (mm)	Maximum payload		Maximum pushing force (N)	Positioning repeatability (mm)	Stroke (mm)			
				Horizontal (kg)	Vertical (kg)						
RCP3-RA2BR-1-20SP-6-①-②-③-④	High thrust	Ball screw	6	1	0.325	See page A-81.	±0.02	25 to 150 (every 25mm)			
RCP3-RA2BR-1-20SP-4-①-②-③-④			4	2	0.625						
RCP3-RA2BR-1-20SP-2-①-②-③-④			2	4	1.25						
RCP3-RA2BR-1-20SP-1-①-②-③-④			1	8	2.5						
RCP3-RA2BR-1-20P-6-①-②-③-④	Standard	Ball screw	6	0.5	0.2						
RCP3-RA2BR-1-20P-4-①-②-③-④			4	1	0.375						
RCP3-RA2BR-1-20P-2-①-②-③-④			2	2	0.75						
RCP3-RA2BR-1-20P-1-①-②-③-④			1	4	1.5						
RCP3-RA2BR-1-20P-6S-①-②-③-④	Standard	Lead screw	6	0.25	0.125				±0.05		
RCP3-RA2BR-1-20P-4S-①-②-③-④			4	0.5	0.25						
RCP3-RA2BR-1-20P-2S-①-②-③-④			2	1	0.5						

#### Stroke and Maximum Speed

Lead	Stroke	25 (mm)	50 (mm)	75~150 (mm)
		Ball screw	6	180
Ball screw	4	180	200	
	2	100		
	1	50		
Lead screw	6	180	280	300
	4	180	200	
	2	100		

Code explanation ① Stroke ② Applicable Controller ③ Cable length ④ Options \*See page A-71 for details on push motion. (Unit: mm/s)

#### ① Stroke

① Stroke (mm)	Standard price		
	Feed screw		
	Ball screw		Lead screw
High thrust type	Standard type		
25	—	—	—
50	—	—	—
75	—	—	—
100	—	—	—
125	—	—	—
150	—	—	—

#### ④ Options

Name	Option code	Page	Standard Price
Brake	<b>B</b>	→ A-42	—
Side-mounted motor to the left (standard)	<b>ML</b>	→ A-52	—
Side-mounted motor to the right	<b>MR</b>	→ A-52	—
Non-motor end specification	<b>NM</b>	→ A-52	—

#### ③ Cable Length

Type	Cable symbol	Standard price
Standard type	<b>P</b> (1m)	—
	<b>S</b> (3m)	—
	<b>M</b> (5m)	—
Special length	<b>X06</b> (6m) ~ <b>X10</b> (10m)	—
	<b>X11</b> (11m) ~ <b>X15</b> (15m)	—
	<b>X16</b> (16m) ~ <b>X20</b> (20m)	—
		—

\* The standard cable for the RCP3 is the robot cable.  
\* See page A-59 for cables for maintenance.

### Actuator Specifications

Item	Description
Drive method	Ball screw/Lead screw, ø6mm, rolled C10
Lost motion	Ball screw: 0.1mm or less/Lead screw: 0.3mm or less (default value)
Base	Material: Aluminum, white alumite treated
Guide	Slide guide
Ambient operating temperature/humidity	0 to 40°C, 85% RH max. (No condensing)
Service life	Lead screw specification
	Ball screw specification

Dimensional Drawings



CAD drawings can be downloaded from the website.

www.intelligentactuator.com

\* The drawing below shows the specification of the motor side-mounted to the left.


For Special Orders

Appendix P.15



(Brake-equipped)

(No brake)



- (\*1) Connect the motor-encoder integrated cable here.
- (\*2) During home return, be careful to avoid interference from peripheral objects because the slider travels until the mechanical end.
- (\*3) The orientation of the bolt varies depending on the product.

Note:  
Do not apply any external force on the rod from any direction other than the direction of the rod's motion. If a force is exerted on the rod in a perpendicular or rotational direction, the detent may become damaged.



ST : Stroke  
ME : Mechanical end  
SE : Stroke end

\* Brake equipped models are 0.1 kg heavier.

■ Dimensions and Weight by Stroke

Stroke	25	50	75	100	125	150
L	111.5	136.5	161.5	186.5	211.5	236.5
A	94.5	119.5	144.5	169.5	194.5	219.5
B	25	50	75	100	125	150
C	0	0	0	50	62.5	75
D	4	4	4	6	6	6
Weight (kg)	0.38	0.41	0.44	0.47	0.5	0.53

② Applicable Controllers

RCP3 series actuators can be operated with the controllers indicated below. Select the type according to your intended application.

Name	External view	Model number	Features	Maximum number of positioning points	Input power	Power-supply capacity	Standard price	Reference page
Solenoid Valve Type		PMEC-C-20SPI-①-2-② PMEC-C-20PI-①-2-②	Easy-to-use controller, even for beginners	3 points	AC100V AC200V	Refer to P541	—	→ P537
		PSEP-C-20SPI-①-2-0 PSEP-C-20PI-①-2-0	Simple controller operable with the same signal as a solenoid valve					→ P547
Solenoid valve multi-axis type PIO specification		MSEP-C-③-④-①-2-0	Positioner type based on PIO control, allowing up to 8 axes to be connected	256 points	DC24V	Refer to P572	—	→ P563
Solenoid valve multi-axis type Network specification		MSEP-C-③-④-⑤-0-0	Field network-ready positioner type, allowing up to 8 axes to be connected					→ P607
Positioner type High-output specification		PCON-CA-20SPI-①-2-0 PCON-CA-20PI-①-2-0	Equipped with a high-output driver Positioner type based on PIO control	512 points	DC24V	Refer to P618	—	→ P623
Pulse-train type High-output specification		PCON-CA-20SPI-PL□-2-0 PCON-CA-20PI-PL□-2-0	Equipped with a high-output driver Pulse-train input type	(—)				
Field network type High-output specification		PCON-CA-20SPI-⑤-0-0 PCON-CA-20PI-⑤-0-0	Equipped with a high-output driver Supporting 7 major field networks	768 points				
Pulse Train Input Type (Differential Line Driver)		PCON-PL-20SPI-①-2-0 PCON-PL-20PI-①-2-0	Pulse train input type with differential line driver support	(—)	DC24V	Refer to P628	—	→ P665
Pulse Train Input Type (Open Collector)		PCON-PO-20SPI-①-2-0 PCON-PO-20PI-①-2-0	Pulse train input type with open collector support					
Serial Communication Type		PCON-SE-20SPI-N-0-0 PCON-SE-20PI-N-0-0	Dedicated Serial Communication	64 points	DC24V	Refer to P671	—	→ P665
Program Control Type		PSEL-CS-1-20SPI-①-2-0 PSEL-CS-1-20PI-①-2-0	Programmed operation is possible. Can operate up to 2 axes	1500 points	DC24V	Refer to P671	—	→ P665

\* This is for the single-axis PSEL. \* ① indicates I/O type (NP/PN). \* ② indicates power supply voltage (1: 100V / 2: 100~240V). \* ③ indicates number of axes (1 to 8). \* ④ indicates field network specification symbol. \* □ indicates N (NPN specification) or P (PNP specification) symbol.