


Field Network Controllers

ROBONET/PCON/ACON/SCON PSEL/ASEL/SSEL/XSEL



Introducing the Network Specification PSEL/ASEL Controllers

All models of the ROBO Cylinder controllers now support field network connection*
*Excludes PCON-CF



Features

The controller can be connected directly to major networks

DeviceNet
CC-Link

ProfiBus

Ethernet

*Ethernet is only supported on XSEL controllers

To control the actuator, all you need is to turn the position number I/O ON via network, and the actuator will move to the specified position

Movement by position number specification

The actuator is operated by turning the I/O signals ON/OFF to specify desired coordinate numbers (position numbers) that have been input to the controller beforehand

The ROBONET, PCON and ACON controllers can operate actuators based on direct specification of target positions as numerical values

Movement by direct numerical specification

The coordinates of the target position are sent via network to move the actuator to position

Functions

| С | ontroller Type | Positioner Type | | | Program Type | | | | |
|------------------------------|---|-----------------------|-------------|-------------|--------------|-------------|-------------|--------------|---|
| Co | ontroller Series | ROBONET | PCON | ACON | SCON | PSEL NEW | ASEL NEW | SSEL | XSEL |
| E | External View | | | | | | | t | Topic on the control of the control |
| Suppo | orted ROBO Cylinders | RCP2/RCP3 RCA/RCA2 | RCP2/RCP3 | RCA/RCA2 | RCS2 | RCP2/RCP3 | RCA/RCA2 | RCS2 | RCS2 |
| Number of Positioning Points | | 768 points* | 768 points* | 768 points* | 512 points | 1500 points | 1500 points | 20000 points | 20000 points |
| | Movement by Position number specification | 0 | 0 | 0 | 0 | 0 | 0 | 0 | 0 |
| Method | Movement by Direct numerical specification | 0 | 0 | 0 | × | × | × | × | × |

^{*} If the actuator is operated based on movement by direct numerical specification, an infinite number of positioning points can be supported.

Note) The ROBONET, PCON, ACON and SCON are supported by PC software and teaching pendants of RCM-101-MW (PC software) Version 6.0.5.0 or later and CON-T (teaching pendant) Version 1.04 or later, respectively. The PSEL, ASEL, ASEL are supported by PC software and teaching pendants of IA-101-X-MW (PC Software) Version 7.2.7.0 or later and SEL-T (teaching pendant) Version 1.02 or later, respectively.

Models

| Network Type | Network Symbol | Model | | |
|--------------|----------------|---------------------------------------|----------|--|
| | | PCON - C (CG) - □ - <u>DV</u> - 0 - 0 | | |
| | | ACON-C (CG) - □ - <u>DV</u> - 0 - 0 | _ | |
| | | SCON-C-□- <u>DV</u> -0-□ | | |
| DeviceNet | DV | PSEL-C-□-□- <u>DV</u> -0-0 | | |
| | | ASEL-C-□-□- <u>DV</u> -0-0 | _ | |
| | | SSEL-C-□-□- <u>DV</u> -0-□ | | |
| | | XSEL <u>DV</u> 0- | _ | |
| | CC | PCON-C (CG) -□ - <u>CC</u> -0-0 | | |
| | | ACON-C (CG) - □ - <u>CC</u> - 0 - 0 | _ | |
| | | SCON-C-U-CC-0-U | | |
| CC-Link | | PSEL-C-□-□- <u>CC</u> -0-0 | | |
| | | ASEL-C-□-□- <u>CC</u> -0-0 | _ | |
| | | SSEL-C-□-□- <u>CC</u> -0-□ | | |
| | | XSEL | _ | |
| | PR | PCON-C (CG) - □- <u>PR</u> -0-0 | | |
| | | ACON-C (CG)-□- <u>PR</u> -0-0 | _ | |
| | | SCON-C-□- <u>PR</u> -0-□ | _ | |
| ProfiBus | | PSEL-C-□-□- <u>PR</u> -0-0 | | |
| | | ASEL-C-□-□- <u>PR</u> -0-0 | <u> </u> | |
| | | SSEL-C-□-□- <u>PR</u> -0-□ | | |
| | | XSEL <u>PR</u> 0 | _ | |
| Ethernet | ET | XSEL | _ | |

Specifications

■ DeviceNet

| Item | Specification | | | | | | |
|-------------------------------|--|---------------------------|--------------------------|------------------------|--|--|--|
| | DeviceNet2.0 | | | | | | |
| Communication Protocol | Group 2 only server | | | | | | |
| | Insulated node operated by network power | | | | | | |
| Baud Rate | 500k/250k/125kbps | | | | | | |
| | Baud Rate | Maximum Network Length | Maximum Branch Length | Total Branch Length | | | |
| Communication | 500kbps | 100m | | 39m | | | |
| Cable Length | 250kbps | 250m | 6m | 78m | | | |
| | 125kbps | 500m | | 156m | | | |
| | Note) When a thick DeviceNet cable is used | | | | | | |
| Communication Power Supply | DC24V (supplied from DeviceNet) | | | | | | |
| Current Draw | Typ.30mA / Max.55mA | | | | | | |
| Number of occupied nodes | 1node | | | | | | |
| Connector | MSTBA2.5/5-G-5.08AU by Phoenix Contact 1 | | | | | | |

The connector on cable end is standard accessory. Phoenix Contact: SMSTB 2.5/5-ST-5.08AU (other than XSEL - P/Q) MSTB 2.5/5-ST-5.08AU (XSEL - P/Q)

■ CC-Link

| Item | Specification | | | | | |
|------------------------------|---|-----|-----|------|------|------|
| Communication Protocol | CC-Link Ver1.10 (Other than ROBONET) / Ver 2.0 (ROBONET) | | | | | |
| Baud Rate | 10M/5M/2.5M/625k/156kbps | | | | | |
| Communication Method | Broadcast polling method | | | | | |
| Number of occupied stations | ASEL/PSEL/SSEL: Up to 3 remote device stations SCON: 1 remote I/O station ROBONET/ACON/PCON: Up to 4 remote device stations | | | | | |
| Communication Cable Length 1 | Baud rate(bps) | 10M | 5M | 2.5M | 625K | 156K |
| | Total cable length (m) | 100 | 160 | 400 | 900 | 1200 |
| Connector *2 | Phoenix Contact: MC1.5/5-G-3.81 (SCON) MSTBA2.5/5-G-5.08AU (XSEL, SSEL, ACON, PCON) | | | | | |

¹ If T-branch communication is to be used, refer to the operation manuals for the master unit and the PLC installed in the master unit.


■ ProfiBus

| Item | Specification | | | |
|------------------------------|---------------------------------|-------|--|--|
| Communication Information | DP Slave | | | |
| Baud Rate | 9.6kbps ~ 12Mbps | | | |
| | 9.6kbps | 1500m | | |
| | 500kbps | 400m | | |
| Communication Cable Length | 1.5Mbps | 200m | | |
| | 3Mbps | 200m | | |
| | 12Mbps | 100m | | |
| Connector | D-sub connector, 9 pins, socket | | | |

■ Ethernet

| Item | Specification | | |
|---------------------------|---|--|--|
| Network | 10BASE-T/100BASE-T (auto negotiation) | | |
| Communication Protocol | IEEE802.3 | | |
| Baud Rate | 10/100Mbps | | |
| Protocol | TCP/IP message communication (IAI protocol B/TCP, SEL program send/receive) | | |
| | Open Modbus/TCP (remote I/O) | | |
| Connector | RJ-45 | | |

^{*2} The connector on the cable end is standard accessory.



Head Office 2690W 237th Street Torrance CA 90505 Chicago Office 1261 Hamilton Parkway Itasca, IL 60143 Atlanta Office 1220 Kennestone Circle, Suite E Marietta, GA 30066



