

ISB-SXM

Single-axis robot/Small, X-axis, standard slider type/Actuator width: 90mm/60W
Straight shape

ISPB-SXM

Single-axis robot/Small, X-axis, standard slider type/Actuator width: 90mm/60W
Straight shape **High precision specification**



Model Specification Items

Series	SXM	Encoder type	Motor type	Lead	Stroke	Applicable controller	Cable length	Options
ISB: Standard specification ISPB: High precision specification		A: Absolute specification I: Incremental specification	60: 60W	16: 16mm 8: 8mm 4: 4mm	100: 100mm ? 900: 900mm (in 50mm increments)	T1: XSEL-J/K T2: SCON SSEL XSEL-P/Q	N: None S: 3m M: 5m X□□: Specified length	Refer to the options table below.

* Refer to P. 10 for the details of items comprising the model number.

Model Number/Specification

Model number	Encoder type	Motor output (W)	Lead (mm)	Stroke in 50mm increments (mm)	Speed (mm/s)	Acceleration (Note 1)				Payload (Note 1)				Rated thrust (N)
						Horizontal (G)		Vertical (G)		Horizontal (kg)		Vertical (kg)**		
						Rated	Maximum	Rated	Maximum	Rated acceleration	Maximum acceleration	Rated acceleration	Maximum acceleration	
ISB[ISPB]-SXM-①-60-16-②-③-④-⑤	Absolute Incremental	60	16	100~900	1~960	0.4	1.2	0.4	0.8	13	3.5	3.5	2	53.1
ISB[ISPB]-SXM-①-60-8-②-③-④-⑤			8		1~480	0.4	0.7	0.4	0.6	27	12	7	5	106.1
ISB[ISPB]-SXM-①-60-4-②-③-④-⑤			4		1~240	0.2	0.5	0.2	0.4	55	30	14	12	212.3

*In the above model numbers, ① indicates the encoder type, ② indicates the stroke, ③ indicates the applicable controller, ④ indicates the cable length, and ⑤ indicates the option(s).
**If the guide with ball retention mechanism (RT) is used, the vertical payload decreases by 0.5kg. (Please also refer to P.9).


Option

Name	Model number	Reference page	Name	Model number	Reference page
Cable exit from the left	A1S	→P11	Home limit switch	L	→P11
Cable exit from the rear left	A1E	→P11	Home limit switch on the opposite side	LL	→P11
Cable exit from the right	A3S	→P11	Master axis specification	LM	→P12
Cable exit from the rear right	A3E	→P11	Master axis specification (sensor on the opposite side)	LLM	→P12
AQ seal (standard feature)	AQ	→P11	Non-motor side specification	NM	→P12
Brake	B	→P11	Guide with ball retention mechanism	RT	→P12
Creep sensor	C	→P11	Slave axis specification	S	→P12
Creep sensor on the opposite side	CL	→P11	High straightness, precision specification	ST	→P13

Common Specifications

Positioning repeatability (Note 2)	±0.01mm (±0.005mm)
Drive method (Note 3)	Ball screw ϕ 12mm, rolled C10 [equivalent to rolled C5]
Lost Motion (Note 4)	0.05mm [0.02mm] max.
Dynamic allowable load moment (Note 5)	Ma: 28.4N·m Mb: 40.2N·m Mc: 65.7N·m
Overhang load length	Ma direction: 450mm max. Mb, Mc directions: 450mm max.
Dynamic straightness (Note 6)	0.02mm/m max.
Base	Material: Aluminum, with white alumite treatment
Applicable controller	T1: XSEL-J/K T2: XSEL-P/Q, SSEL, SCON
Cable length (Note 7)	N: None, S: 3m, M: 5m, X□□: Specified length
Ambient operating temperature/humidity	0 to 40°C, 85%RH max. (non-condensing)

Diagram



Dimensions, Mass and Maximum Speed by Stroke

Stroke	100	150	200	250	300	350	400	450	500	550	600	650	700	750	800	850	900
	L without brake	344	394	444	494	544	594	644	694	744	794	844	894	944	994	1044	1094
L with brake	379	429	479	529	579	629	679	729	779	829	879	929	979	1029	1079	1129	1179
A	100	150	200	250	300	350	400	450	500	550	600	650	700	750	800	850	900
B	251	301	351	401	451	501	551	601	651	701	751	801	851	901	951	1001	1051
C	0	0	0	1	1	1	1	2	2	2	2	3	3	3	3	4	4
D	151	201	251	101	151	201	251	101	151	201	251	101	151	201	251	101	151
E	4	4	4	6	6	6	6	8	8	8	8	10	10	10	10	12	12
F	151	201	251	301	351	401	451	501	551	601	651	701	751	801	851	901	951
G	131	131	181	231	281	331	381	431	481	531	581	631	681	731	781	831	881
H	0	0	0	0	0	0	1	1	1	1	2	2	2	2	3	3	3
J	56	56	106	156	206	256	106	156	206	256	106	156	206	256	106	156	206
K	0	50	50	50	50	50	50	50	50	50	50	50	50	50	50	50	50
P	8	10	10	10	10	10	12	12	12	12	14	14	14	14	16	16	16
Mass (kg)	3.0	3.4	3.8	4.2	4.5	4.9	5.2	5.6	5.9	6.3	6.6	7.0	7.3	7.7	8.0	8.4	8.7
Maximum speed (mm/s)	Lead 16	960															
	Lead 8	480															
	Lead 4	240															
													655	515	415		
													330	260	210		
													165	130	100		

Applicable Controller Specifications

Applicable Controller	Maximum number of controlled axes	Connectable encoder type	Operating method	Power-supply voltage	Reference page
X-SEL-P/Q	6 axes	Absolute/incremental	Program	Single/three-phase 200 VAC	→P56
X-SEL-J/K	4 axes			Single-phase 100/200 VAC	→P56
SSEL	2 axes			→P56	
SCON	1 axis			→P56	

CAUTION

(Note 1) Refer to P.9 for the relationship of acceleration and payload. (Notes 2, 3, 4)

(Note 5) The values in [] apply to the ISPB series. Other specification values apply commonly to the ISB and ISPB.

(Note 6) When the traveling life is 10,000km.

(Note 7) The value of dynamic straightness is when the high straightness, precision specification (option) is specified. The maximum cable length is 30m. Specify a desired length in meters. (Example. X08 = 8m)