




Dimensions – Sideway Specification

You can download CAD drawings from our website.

2D CAD

\*1 During home return, the slider will move to the ME. Accordingly, pay attention to possible contact between the slider and surrounding structures, etc.  
ME: Mechanical end  
SE: Stroke end



| Stroke      | 40  | 88  | 136 | 184 | 232 | 280 | 328 | 376 | 424 | 472 | 520  | 568  | 616  | 664  | 712  | 760  | 808  | 856  | 904  | 952  | 1000 | 1048 |
|-------------|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|------|------|------|------|------|------|------|------|------|------|------|------|
| L           | 526 | 574 | 622 | 670 | 718 | 766 | 814 | 862 | 910 | 958 | 1006 | 1054 | 1102 | 1150 | 1198 | 1246 | 1294 | 1342 | 1390 | 1438 | 1486 | 1534 |
| A           | 2   | 2   | 2   | 2   | 3   | 3   | 3   | 3   | 3   | 4   | 4    | 4    | 4    | 5    | 5    | 5    | 5    | 6    | 6    | 6    | 6    | 7    |
| B           | 20  | 68  | 116 | 164 | 12  | 60  | 108 | 156 | 204 | 52  | 100  | 148  | 196  | 44   | 92   | 140  | 188  | 36   | 84   | 132  | 180  | 28   |
| C           | 12  | 12  | 12  | 12  | 16  | 16  | 16  | 16  | 16  | 20  | 20   | 20   | 20   | 24   | 24   | 24   | 24   | 28   | 28   | 28   | 28   | 32   |
| D           | 320 | 368 | 416 | 464 | 512 | 560 | 608 | 656 | 704 | 752 | 800  | 848  | 896  | 944  | 992  | 1040 | 1088 | 1136 | 1184 | 1232 | 1280 | 1328 |
| Weight (kg) | 6.4 | 6.6 | 6.8 | 7.0 | 7.2 | 7.4 | 7.6 | 7.8 | 8.0 | 8.2 | 8.5  | 8.7  | 8.9  | 9.1  | 9.3  | 9.5  | 9.7  | 9.9  | 10.1 | 10.3 | 10.5 | 10.8 |

Shaft type

Small type

Flat type

Medium type

Large type